

产品认证证书

II型自愿认证

证书编号: CQC2017010305956450

发证日期: 2021年01月07日

有效期至: 2031年08月30日

委托人名称 ABB 新会低压开关有限公司
及注册地址 广东省江门市新会区今古洲工业开发区

制造商名称 ABB 新会低压开关有限公司
及注册地址 广东省江门市新会区今古洲工业开发区

生产企业名称 ABB 新会低压开关有限公司
及生产地址 广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 双电源转换开关
OTM□F□□□□C□; 具体参数及型号解释见附件

产品标准和技术要求 GB/T 14048.11-2016


认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

陈昕

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0098696

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2017010305956450

Valid from: Jan.07,2021

Valid until: Aug.30,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone Xinhui Region,Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Transfer Switching_equipment OTM□F□□□□C□ ; See the attachment for the detailed parameters and model explanation
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.11-2016
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

陈昕

SIGNATURE

谢肇煦

CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0098696

产品认证证书

II型自愿认证

附 录

证书编号: CQC2017010305956450

第 1 页 共 2 页

纸 号: 98696

OTM□F□□□□C□;

Ui: 750V; Uimp : 8kV; Ith : 125A;

Ue: AC220/230/240V (2P), AC380/400/415V (3P/4P);

Ie: 32A、40A、50A、63A、80A、100A、125A

(AC-33B 使用类别时, 100A、125A 需降容到 80A);

使用类别: AC-31B/AC-32B/AC-33iB/AC-33B;

Iq : 50kA;

电器级别: PC 级;

转换方式: ATSE;

极数: 2P、3P、4P;

控制器 Uimp : 6kV;

注: 此附录与证书同时使用时有效。



中国质量认证中心



产品认证证书

II型自愿认证

附 录

证书编号: CQC2017010305956450

第 2 页 共 2 页

纸 号: 98696

型号的解释:

OTM ☐ F ☐ ☐ ☐ ☐ C ☐

特征值

空白: 默认型号, A~Z: 特殊客户

交流: AC

操作机构工作电压 (V):

2P: 220、230、240,

3P/4P: 380、400、415

控制器型号:

20D、12D、12T、21D、21T

转换开关

C: 上进线, CB: 下进线

极数: 2: 2P、3: 3P、4: 4P

设计序列号

额定电流 (A) : 32、40、50、63、80、100、125

产品系列号

注: 此附录与证书同时使用时有效。



中国质量认证中心

