

产品认证证书

II型自愿认证

证书编号: CQC2018010304040898

发证日期: 2021年10月09日

有效期至: 2031年10月09日

委托人名称 ABB 新会低压开关有限公司
及注册地址 广东省江门市新会区今古洲工业开发区

制造商名称 ABB 新会低压开关有限公司
及注册地址 广东省江门市新会区今古洲工业开发区

生产企业名称 ABB 新会低压开关有限公司
及生产地址 广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 接触器
A2X52,A2X65,A2X80,A2X96; 规格参数详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

签发

刘江

谢肇煦



中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0105645

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2018010304040898

Valid from: Oct.09,2021

Valid until: Oct.09,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	contactor A2X52,A2X65,A2X80,A2X96; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

刘江

SIGNATURE

谢肇熙



CHINA QUALITY CERTIFICATION CENTRE



<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666

C(2) 0105645

产品认证证书

II型自愿认证

证书编号: CQC2018010304040898

第1页 共4页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105645

上报参数:

A2X52,A2X65,A2X80,A2X96

Ui:690V;

Uimp: 6kV;

Ith:A2X52:80A,A2X65:110A,A2X80:120A,A2X96:125A;

Ue/Ie:

AC-1:A2X52:AC690V/80A;A2X65:AC690V/110A;A2X80:AC690V/120A;

A2X96:AC690V/125A;

AC-3:A2X52:AC220-240V/53A,AC380-400V/53A,AC415V/53A;

A2X65:AC220-240V/65A,AC380-400V/65A,AC415V/65A;

A2X80:AC220-240V/80A,AC380-400V/80A,AC415V/80A;

A2X96:AC220-240V/96A,AC380-400V/96A,AC415V/96A;

使用类别:AC-1,AC-3;

Us:AC24V 50/60Hz,AC48V 50/60Hz,AC110V 50/60Hz,AC220V 50Hz/AC230V 60Hz,

AC380V 50Hz/AC400V 60Hz;

极数:3P;

IP10;

配用的辅助触头: (外置)

CAL5 或 CAL5X

1NO1NC

Ith:16A;

AC-15:Ue/Ie:AC24~127V/6A,AC220~240V/4A,AC380~440V/3A,AC500~690V/2A;

DC-13:Ue/Ie:DC24V/6A, DC48V/2.8A, DC72V/1A, DC110V/0.55A, DC125V/0.55A,

DC220V/0.3A, DC250V/0.3A;



中国质量认证中心



产品认证证书


II型自愿认证

证书编号: CQC2018010304040898

本证书及附件应同时使用, 信息查验说明见证书页

第2页 共4页

纸号: 105645



中国质量认证中心



产品认证证书

II型自愿认证


证书编号: CQC2018010304040898

第3页 共4页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105645

型号解释:



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2018010304040898

第 4 页 共 4 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105645

控制线圈代码 Code of control circuit:

额定工作电压 (Vac) Rated operational voltage (Vac)		线圈代码 Winding code
50Hz	60Hz	
220	230	25
24	24	20
48	48	22
110	110	23
380	400	13



中国质量认证中心

