



产品认证证书

证书编号: CQC2019010303266348

申请人名称及地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

制造商名称及地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称及地址

EOLANE TEMARA (V054940)
lot 14- Zone Industrielle Massira I - 12000 Temara Morocco

产品名称和系列、规格、型号

继电器

OB_OC..., OB_IC..., OB_OA..., Ui:250V(OB_OC..., OB_IC...), 440V(OB_OA...); Uimp:2.5kV(OB_OC..., OB_IC...),
4kV(OB_OA...); Ith:
0.1A(OB_IC0100), 2A(OB_OC2000), 5A(OB_OC5000), 1A(OB_OA1000), 2A(OB_OA2000); OB_IC0100:DC-12:Ue/Ie:58V/0.1A; O
B_OC2000:DC-12:Ue/Ie:58V/2A; OB_OC5000:DC-12:Ue/Ie:58V/5A; OB_OA1000:AC-12:Ue/Ie:400V/1A; OB_OA2000:AC-12:Ue
/Ie:400V/2A; 外壳防护等级:IP20; 型号解释见附件

产品标准和技术要求

GB/T14048.5-2017

认证模式

型式试验+获证后监督

上述产品符合 CQC11-462142-2019 认证规则的要求, 特发此证。

发证日期: 2020 年 09 月 02 日 有效期至: 2022 年 01 月 24 日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

C 0356136



PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2019010303266348

NAME AND ADDRESS OF THE APPLICANT

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE FACTORY

EOLANE TEMARA (V054940)
lot 14- Zone Industrielle Massira I - 12000 Temara Morocco

PRODUCT NAME, MODEL AND SPECIFICATION

Relay

OB_OC..., OB_IC..., OB_OA...; Ui:250V(OB_OC..., OB_IC...), 440V(OB_OA...); Uimp:2.5kV(OB_OC..., OB_IC...),
4kV(OB_OA...); Ith:
0.1A(OB_IC0100), 2A(OB_OC2000), 5A(OB_OC5000), 1A(OB_OA1000), 2A(OB_OA2000); OB_IC0100:DC-12:Ue/Ie:58V/0.1A; OB
_OC2000:DC-12:Ue/Ie:58V/2A; OB_OC5000:DC-12:Ue/Ie:58V/5A; OB_OA1000:AC-12:Ue/Ie:400V/1A; OB_OA2000:AC-12:Ue/Ie:
400V/2A; IP20; See the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.5-2017

TYPE OF CERTIFICATION SCHEMES

Type testing+Follow up factory inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification
rules of CQC11-462142-2019 .

Valid from: Sep.02,2020

Valid until: Jan.24,2022

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing
certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:

Lu Mei



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0356136



产品认证证书

附录

第 1 页 共 1 页

证书编号: CQC2019010303266348

纸 号: 356136

型号解释:

R600 Boxed Interface Optocouplers: NOMENCLATURE - BREAKDOWN							
R600 光电耦合继电器: 命名规则							
Example: 举例	OB	R	I	C	0100	-	230VUC
	I	II	III				IV

I	Opto series 光电耦合系列	Boxed Interface Optocouplers R600 (光电耦合继电器 R600)	
II	Terminal Type (端子类型)	empty (空):	screw terminal (螺钉端子)
		R:	spring terminal (弹簧端子)
III	Type of switch component Current Rating	IC 0100	Transistor DC output 100mA (晶体管直流输出 100 mA)
		OC 2000	MOSFET DC output 2A (MOSFET 直流输出 2 A)
		OC 5000	MOSFET DC output 5A (MOSFET 直流输出 5 A)
		OA 1000	TRIAC AC output 1A (TRIAC 交流输出 1 A)
		OA 2000	TRIAC AC output 2A (TRIAC 交流输出 2 A)
IV	Coil voltages (线圈电压)	DC-Version (直流型号)	AC/DC-Version (交直流通用型号)
		5-12 V DC	24 V UC
		24 V DC	48-60 V UC
			115 V UC
			230 V UC
			115-230 V UC

注: 此附录与证书同时使用时有效。

主任:

陆梅



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>