产品认证证书

II型自愿认证

证书编号：CQC2019010307150164

发证日期：2022年03月22日

有效期至：2032年03月21日

委托人名称及注册地址	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
制造商名称及注册地址	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
生产企业名称及生产地址	ABB S.P.A. Via Enrico Fermi n°40, 03100Frosinone Italy
产品名称和系列、规格、型号	塑料外壳式断路器 XT7S, XT7H, XT7L, XT7S M, XT7H M, XT7L M;详见附件
产品标准和技术要求	GB/T 14048.2-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年09月02日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 签发

中国质量认证中心

C(2) 0151695

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2019010307150164

Valid from: Mar.22,2022

Valid until: Mar.21,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
NAME AND LOCATION OF THE FACTORY	ABB S.P.A. Via Enrico Fermi n°40, 03100Frosinone Italy
PRODUCT NAME, MODEL AND SPECIFICATION	Moulded case circuit-breaker XT7S, XT7H, XT7L, XT7S M, XT7H M, XT7L M;See the appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.2-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Sep.02,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 陈昕

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0151695

产品认证证书

II型自愿认证

证书编号：CQC2019010307150164

本证书及附件应同时使用，信息查验说明见证书页

纸号：151695

XT7S, XT7H, XT7L,XT7S M, XT7H M, XT7L M

Uimp:8kV;

Ui:1000V;

Ue: AC220V, AC230V, AC240V, AC380V, AC400V, AC415V, AC440V, AC500V, AC525V, AC660V, AC690V;

In: 400A, 600A, 630A, 800A, 1000A, 1200A, 1250A, 1600A;

Ics, Icu 和 Icw 如下表：

	XT7S XT7S M	XT7H XT7H M	XT7L XT7L M
Icu 220-230-240Vac [kA]	85	100	200
Icu 380-400-415Vac [kA]	50	70	120
Icu 440Vac [kA]	50	65	100
Icu 500Vac [kA]	45	50	85
Icu 525Vac [kA]	45	50	65
Icu 660-690Vac [kA]	30	42	50
Ics 220-230-240Vac [kA]	85	100	200
Ics 380-400-415Vac [kA]	50	70	120
Ics 440Vac [kA]	50	65	100
Ics 500Vac [kA]	45	50	85
Ics 525Vac [kA]	45	50	65
Ics 660-690Vac [kA]	30	42	50
Icw [kA 1s]	20	20	20

频率: 50/60Hz;

选择性类别: B 类;

过电流脱扣器类型: 电子式;

适用于隔离;

极数: 3P, 4P

辅助触头: CQC21107322161

2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC;

Ith: 16A

AC-12: Ue/Ie: 250V/16A, 125V/16A, 250V/10A, 125V/10A, 250V/8A, 125V/8A, 250V/6A, 125V/6A, 400V/3A;

DC-12: Ue/Ie: 250V/0.3A,125V/0.6A;

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2019010307150164

本证书及附件应同时使用，信息查验说明见证书页

纸号：151695

辅助触头(本体): 2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC
Ith: 16A
AC-12: Ue/Ie: 400V/3A;
AC-14: Ue/Ie: 400V/3A, 250V/10A;
DC-12: Ue/Ie: 24V/0.1A;
DC-13: Ue/Ie: 250V/0.15A,125V/0.3A
符合附录 N 的电子附件：
闭合线圈：YC; Us:24VAC/DC, 30VAC/DC, 48VAC/DC, 60VAC/DC, 110-120VAC/DC, 120-127VAC/DC, 220-240VAC/DC, 240-250VAC/DC, 380-400VAC, 415-440VAC, 480-500VAC 50/60Hz
欠压脱扣器：YU; Us: 24VAC/DC, 30VAC/DC, 48VAC/DC, 60VAC/DC, 110-120VAC/DC, 120-127VAC/DC, 220-240VAC/DC, 240-250VAC/DC, 380-400VAC, 415-440VAC, 480-500VAC 50/60Hz;
分励脱扣器：YO; Us: 24VAC/DC, 30VAC/DC, 48VAC/DC, 60VAC/DC, 110-120VAC/DC, 120-127VAC/DC, 220-240VAC/DC, 240-250VAC/DC, 380-400VAC, 415-440VAC, 480-500VAC 50/60Hz

中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2019010307150164

本证书及附件应同时使用，信息查验说明见证书页

纸号：151695

型号解释：





中国质量认证中心