
 TECHNICAL DATA SHEET

8" Recessed Poke-Through

RPT-8

Steel City®


Steel City® RPT8, 5-gang recessed poke-through floor box

Certifications / Standards:


Features:

- 5 gangs in recessed compartments
- No hinge design
- 4 finish options
- Conduit knockouts, sizes 3/4", 1", 1 1/4", 1 1/2" & 2"
- 1" NPS

Ratings:

- 50 Amp maximum center device
- 2 Hour Fire Rating
- 0.131 in² maximum copper wire area
- 124 in³ maximum junction box volume

Conforms to:

- UL 514A & 263
- CSA C22.2 & 18.1
- City of Chicago CCEA

Product selection				
Drawing	Part number	Description	Cover Material /Finish	Chicago Approved
	RPT8-5G-ALM	5 Gang recess poke-through	Aluminum, Brushed	—
	RPT8-5G-BRS	5 Gang recess poke-through	Brass, Machined	—
	RPT8-5G-BLK	5 Gang recess poke-through	Aluminum, Black (powder coated)	—
	RPT8-5G-SN	5 Gang recess poke-through	Brass, Satin nickel plated	—
	RPT8-5G-ALMC	5 Gang recess poke-through	Aluminum, Brushed	Yes
	RPT8-5G-BRSC	5 Gang recess poke-through	Brass, Machined	Yes
	RPT8-5G-BLKC	5 Gang recess poke-through	Aluminum, Black (powder coated)	Yes
	RPT8-5G-SNC	5 Gang recess poke-through	Brass, Satin nickel plated	Yes

Note: Product must be installed in accordance with applicable national and local electrical codes.

 ABB Installation Products
 Memphis, Tennessee
 USA

 We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

 We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB Installation Products. Copyright © 2018 ABB Installation Products. All rights reserved.

 Let's write the future.
 Together. abb.com