

TECHNICAL DATA SHEET

Push Mount Cable Tie

High temperature and flame retardant

Ty-Fast®

Certifications / Standards:

Features

- One-piece molded design
- Integrated Arrow Head Mount
- Precision locking mechanism
- Easy Installation

Materials:


- Polyamide (Nylon) 6.6
- Heat Resistant Black
- Flame Retardant

Ratings:

- Operating Temperature: -40°C to 125°C
- Minimum Installation Temperature: 0°C

Conforms to:

- Flammability: V0 per GB/T2408-2008
- RoHS and REACH Complaint
- Halogen and Silicon Free


Product selection

Catalog No	T1 in (mm)	T2 in (mm)	T3 in (mm)	W1 in (mm)	W2 in (mm)	W3 in (mm)	L1 in (mm)	L2 in (mm)	Tensile Strength (lbs/N)	Max Bundle Dia. (mm)	Panel Thickness in (mm)	Mounting Hole Dia. D in (mm)
TY200-50X-PMHV-50	0.100 (1.25)	0.20 (5.0)	0.14 (3.5)	0.19 (4.8)	0.30 (8.2)	0.24 (6.2)	7.7 (196)	0.27 (6.9)	50 (220)	2.0 (50)	0.067-0.077 (1.70-1.95)	0.19 - 0.23 (4.8 - 5.9)
TY200-50X-PMHV												

Note: Product must be installed in accordance with applicable national and local electrical codes. For best results an approved installation tool should be used. Product should be stored in sealed package at 23°C and 50% relative humidity away from direct heat sources and out of direct sunlight.
Recommended installation tool: ERG50

ABB Installation Products
Memphis, Tennessee
USA

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB Installation Products. Copyright© 2018 ABB Installation Products. All rights reserved.

Let's write the future.
Together. **abb.com**