

---

**TECHNICAL DATA SHEET**

# Drain adapter, stainless steel

Part number: FG-DA-3/8

## T&B® Fittings



Drain adapter, helps drain accumulated moisture or small debris from stainless steel enclosures.

### Certifications / Standards:




---

### Features:

- Compact body design and special-grade silicone gasket makes the drain adapter suitable for installation in tight spaces and on curved surfaces
- Large drain orifices, an integral breather reduces clogging, even when exposed to viscous liquids or small debris
- No moving parts ensures long-lasting performance
- 1/4" female NPT threaded connection for assembling a drain tube
- Drain adapter used in conjunction with the T&B ball valve, offers a UL Type 4X rating, IP69 and is suitable for wash down areas
- 9/16" wrench flats

---

### Applications:

- For use on stainless steel electrical enclosures
- Food and beverage facilities
- Can be used with T&B® stainless steel ball valve, part no. DBV-1/4

---

### Conforms to:

- cULus Listed, Type 4x, when assembled with T&B® ball valve, DBV-1/4
- NSF Certified per NSF/ANSI Standard 169 for food and beverage applications
- FDA compliant material

---

### Materials / Finishes:

- Stainless Steel, Type 316 (corrosion resistance)

