

TECHNICAL DATA SHEET - INTERACTIVE PDF

Compression Tool, 6 Ton Hydraulic

TBM62CR-LI, inline, closed head

T&B° Tools



6 ton 18V battery powered inline, closed head, compression tool for use on compression lugs and splices.

3-Part Specification: End User Tools

Features

- TBM62CR-LI is a fully automatic, self-contained power tool for effortless compression
- Compatible with MAKITA LXT 18V battery platform $\!\!\!\!\!\!^*$
- Patent pending user-selectable auto-retract feature
- One handed operation to help control ram advancement and retraction
- 180 degree rotating head
- Tool kit contents include:
 - Compression tool
 - 2 batteries (one 5ah and one 2ah)
 - Battery charger
 - Operation instructions
 - Carrying bag

Conforms to:

UL 486A-B when used with Color-Keyed® connectors

Specifications:

- · Weight: 5.9 lbs
- Dimensions: 15.8"H x 4.5"L x 3.3"W
- Battery: 18V, 5.0ah MAKITA LXT Lithium Ion*
- Charger: 120V AC Input
- Accepts 6Ton Series Dies
- Compression force: 6 tons
- · Capacity: 600 kcmil Cu / 400 kcmil Al

Dies for standard lugs & splices TBM62CR-LI 6 ton hydraulic tool

Product selection							
Conductor size			Die Code / Color-Keyed®	Die	Die	Hex-Flex® die	Hex-Flex® die
Code copper	Flex/24	AL/CU	connector color code	Part no.	Code no.	Part no.	Code no
8 AWG	37/24	10 AWG	Red	6TON21SS	21	6TON21XSS	21)
6 AWG	61/24	8 AWG	Blue	6TON24SS	24	6TON24XSS	24)
4 AWG	91/24	6 AWG	Gray	6TON29SS	29	6TON29XSS	29>
2 AWG	125/24	_	Brown	6TON33SS	33	6TON33XSS	33)
1 AWG	140/24	4 AWG	Green	6TON37SS	37	6TON37XSS	37)
1/0	225/24	2 AWG	Pink	6TON42SS	42	6TON42XSS	42)
2/0	275/24	_	Black	6TON45SS	45	6TON45XSS	45)
3/0	325/24	_	Orange	6TON50SS	50H	6TON50XSS	50>
4/0	450/24	_	Purple	6TON54SS	54H	6TON54XSS	54)
250 kcmil	550/24	_	Yellow	6TON62SS	62H	6TON62XSS	62)
_	_	1 AWG	Gold	6TON45SS	45	_	_
_	_	1/0	Tan	6TON50SS	50H	_	_
_	_	2/0	Olive	6TON54SS	54H	_	_
_	_	3/0	Ruby	6TON60SS	60H	_	_
300 kcmil	650/24	4/0	White	6TON66SS	66H	6TON66XSS	66)
350 kcmil	775/24 (short)	250 kcmil	Red	6TON71SS	71H	_	_
400 kcmil	775/24 (long)	300 kcmil	Blue	6TON76SS	76H	_	_
_	925/24*	_		6TON80SS	80H	_	_
500 kcmil	_	350 kcmil	Brown	6TON87SS	87H	_	_
600 kcmil	1100/24	400 kcmil	Green	6TON94SS	94H	_	_

 $Note: Product\ must\ be\ installed\ in\ accordance\ with\ applicable\ national\ and\ local\ electrical\ codes.$

*Standard barrel only. Long barrel requires Brown 87H.

**Standard barrel only. Long barrel requires Black 106H.

For the bottom half (the indenter), order one Cat. No. 6TONXSS for all 6TONX Series