PLC AUTOMATION

Product information

CP600 platform FW / programming SW Overview



CP600 platform control panels, relevant production indexes, FW versions and suitable PB610 versions.

–
CP600 platform

This document summarizes the FW / SW versions and production indexes from the CP600 platform control panels. It informs about the dependencies between devices/FW/SW versions.

Any liability of ABB – regardless of the legal grounds – shall be excluded. In particular any warranty or defect liability for the Products (whether hardware, software or firmware) or for any documentation or information related thereto and any damage or losses resulting there from shall be excluded, e.g. in view of correctness, completeness, applicability of the Products/documentation/information or the same not being up-to-date and free of any defect.

CP600-eCo, CP600 and CP600-Pro: Dependencies between devices, FW, SW

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP604	A0	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.161 BASIC	1.2.0/ 1.2.1 1.2.2	n.a.
CP604	A0	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.215 BASIC	1.2.3	n.a.
CP604	A1	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.1.243	1.2.4	n.a.
CP604	B1	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP604	B1	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP604	B1	1SAP504100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP604-B	A1	1SAP504100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.

Product	Index	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP604-B	A1	1SAP504100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP607	A0	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.161 BASIC	1.2.0/1.2.1 1.2.2	n.a.
CP607	A0	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.215 BASIC	1.2.3	n.a.
CP607	A1	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.1.243	1.2.4	n.a.
CP607	B1	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP607	B1	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP607	B1	1SAP507100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP607-B	A1	1SAP507100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP607-B	A1	1SAP507100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP610	A0	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.161 BASIC	1.2.0/1.2.1 1.2.2	n.a.
CP610	A0	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.0.215 BASIC	1.2.3	n.a.
CP610	A1	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.0	V2.0.1.243	1.2.4	n.a.
CP610	B1	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP610	B1	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP610	B1	1SAP510100R0001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP610-B	A1	1SAP510100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP610-B	A1	1SAP510100R2001	CP600-eCo	Linux 3.12	UN60, V1.0.37	V2.6.1.175	2.1.2	n.a.
CP620	A0	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	V1.58.0.22	n.a.	n.a.
CP620	A1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	n.a.	n.a.
CP620	B0	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP620	B1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.
CP620	B2	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP620	C1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP620	C2	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.

Product	Index	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP620	C3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP620	D1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP620	G1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	1.1.1	n.a.
CP620	H1	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.2.3	n.a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	2.0.0/2.0.1	n.a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	2.0.2	n.a.
CP620	H3	1SAP520100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP620	A1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	n.a.	n.a.
CP620	B0	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP620	B1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.
CP620	B2	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP620	C1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP620	C2	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP620	C3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP620	D1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP620	G1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	1.1.1	n.a.
CP620	H1	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.2.3	n.a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	2.0.0/2.0.1	n.a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	2.0.2	n.a.
CP620	H3	1SAP520100R4001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.0.3/2.0.4	n.a.
CP620-WEB	A0	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	n.a.	2.1.0/2.1.1	V1.5.15.122
CP620-WEB	A1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	n.a.	2.1.2	V1.5.15.122

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP620-WEB	B0	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.541	n.a.	n.a.	V1.5.15.125
CP620-WEB	B1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	n.a.	n.a.	V1.5.15.131b
CP620-WEB	C1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP620-WEB	C2	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP620-WEB	D1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	n.a.	n.a.	V1.5.15.131b
CP620-WEB	H1	1SAP520200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	n.a.	n.a.	V1.5.15.131b
CP630	A0	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	V1.58.0.22	n.a.	n.a.
CP630	A1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	1.2	n.a.
CP630	B0	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP630	B1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.
CP630	B2	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP630	C1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP630	C2	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP630	C3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP630	D1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP630	G1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	n.a.	n.a.
CP630	H1	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	n.a.	n.a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.1.1	n.a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	1.2	n.a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	1.2.3	n.a.
CP630	H3	1SAP530100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.0.0/2.0.1	n.a.
CP630-WEB	A0	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	n.a.	2.0.2	V1.5.15.122
CP630-WEB	A1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	n.a.	2.0.3/2.0.4	V1.5.15.122
CP630-WEB	B0	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.541	n.a.	2.1.0/2.1.1	V1.5.15.125

Product	Index	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP630-WEB	B1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	n.a.	n.a.	V1.5.15.131b
CP630-WEB	C1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP630-WEB	C2	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP630-WEB	D1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	n.a.	n.a.	V1.5.15.131b
CP630-WEB	H1	1SAP530200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	n.a.	1.2	V1.5.15.131b
CP635	A0	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	V1.58.0.22	n.a.	n.a.
CP635	A1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	n.a.	n.a.
CP635	B0	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP635	B1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.
CP635	B2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP635	C1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	C2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	C3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	D1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP635	G1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	1.1.1	n.a.
CP635	H1	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP635	H2	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.2.3	n.a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP635	H3	1SAP535100R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.1.2	n.a.
CP635	A1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	n.a.	n.a.
CP635	B0	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP635	B1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP635	B2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP635	C1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	C2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	C3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635	D1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP635	G1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	1.1.1	n.a.
CP635	H1	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP635	H2	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.2.3	n.a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP635	H3	1SAP535100R5001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.1.2	n.a.
CP635-B	A1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	V1.58.0.22	n.a.	n.a.
CP635-B	B0	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.58.0.22	n.a.	n.a.
CP635-B	B1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.1	n.a.	n.a.
CP635-B	B2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	V1.80.2	n.a.	n.a.
CP635-B	C1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635-B	C2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635-B	C3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	V1.90.0	n.a.	n.a.
CP635-B	D1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.90.0.975	n.a.	n.a.
CP635-B	G1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	V1.91.0	1.1.1	n.a.
CP635-B	H1	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0	1.2	n.a.
CP635-B	H2	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.0	1.2	n.a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.0.1.243	1.2.3	n.a.

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP635-B	H3	1SAP535100R2001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	V2.6.1.175	2.1.2	n.a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP635-FB	A0	1SAP535110R6001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP635-FW	A0	1SAP535110R1001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP635-WEB	A0	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.38	n.a.	n.a.	V1.5.15.122
CP635-WEB	A1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.45	n.a.	n.a.	V1.5.15.122
CP635-WEB	B0	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.541	n.a.	n.a.	V1.5.15.125
CP635-WEB	B1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.54	n.a.	n.a.	V1.5.15.131b
CP635-WEB	C1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP635-WEB	C2	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.66	n.a.	n.a.	V1.5.15.131b
CP635-WEB	D1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.76	n.a.	n.a.	V1.5.15.131b
CP635-WEB	H1	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	n.a.	1.2	V1.5.15.131b
CP635-WEB	H2	1SAP535200R0001	CP600	Win Embedd. CE 6.0 Core	UN31, V1.96	n.a.	1.2	V1.5.15.131b
CP650	A0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	V1.58.0.22	n.a.	n.a.
CP650	B0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.58.0.22	n.a.	n.a.
CP650	B1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.1	n.a.	n.a.
CP650	B2	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.2	n.a.	n.a.
CP650	C0	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.80.2	n.a.	n.a.
CP650	C1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.

Product	Index	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP650	C2	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.
CP650	D1	1SAP550100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	V1.90.0.975	n.a.	n.a.
CP650-WEB	A0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	n.a.	n.a.	V1.5.15.122
CP650-WEB	B0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	n.a.	n.a.	V1.5.15.125
CP650-WEB	C0	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.125
CP650-WEB	C1	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.131b
CP650-WEB	D1	1SAP550200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	n.a.	n.a.	V1.5.15.131b
CP651	A0	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.90.0.975	n.a.	n.a.
CP651	B1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.91.0	1.1.1	n.a.
CP651	C1	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP651	C2	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.1.243	1.2.3	n.a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP651	C3	1SAP551100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP651-WEB	A0	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	n.a.	n.a.	V1.5.15.131b
CP651-WEB	C1	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP651-WEB	C2	1SAP551200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP660	A0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	V1.58.0.22	n.a.	n.a.
CP660	B0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.58.0.22	n.a.	n.a.
CP660	B1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.1	n.a.	n.a.
CP660	B2	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.2	n.a.	n.a.
CP660	C0	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.80.2	n.a.	n.a.
CP660	C1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP660	C2	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.
CP660	D1	1SAP560100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	V1.90.0.975	n.a.	n.a.
CP660-WEB	A0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	n.a.	n.a.	V1.5.15.122
CP660-WEB	B0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	n.a.	n.a.	V1.5.15.125
CP660-WEB	C0	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.125
CP660-WEB	C1	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.131b
CP660-WEB	D1	1SAP560200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	n.a.	n.a.	V1.5.15.131b
CP661	A0	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.90.0.975	n.a.	n.a.
CP661	B1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.91.0	1.1.1	n.a.
CP661	C1	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP661	C2	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.1.243	1.2.3	n.a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP661	C3	1SAP561100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP661-WEB	A0	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	n.a.	n.a.	V1.5.15.131b
CP661-WEB	C1	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP661-WEB	C2	1SAP561200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP665	A0	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.90.0.975	n.a.	n.a.
CP665	B1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.91.0	1.1.1	n.a.
CP665	C1	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP665	C2	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.1.243	1.2.3	n.a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.

Product	In-dex	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.
CP665	C3	1SAP565100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP665-WEB	A0	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	n.a.	n.a.	V1.5.15.131b
CP665-WEB	C1	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP665-WEB	C2	1SAP565200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP675	A0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	V1.58.0.22	n.a.	n.a.
CP675	B0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.58.0.22	n.a.	n.a.
CP675	B1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.1	n.a.	n.a.
CP675	B2	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	V1.80.2	n.a.	n.a.
CP675	C0	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.80.2	n.a.	n.a.
CP675	C1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.
CP675	C2	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	V1.90.0	n.a.	n.a.
CP675	D1	1SAP575100R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	V1.90.0.975	n.a.	n.a.
CP675-WEB	A0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.58	n.a.	n.a.	V1.5.15.122
CP675-WEB	B0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.65	n.a.	n.a.	V1.5.15.125
CP675-WEB	C0	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.125
CP675-WEB	C1	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.73	n.a.	n.a.	V1.5.15.131b
CP675-WEB	D1	1SAP575200R0001	CP600	Win Embedd. CE 6.0 Core	UN20, V2.80	n.a.	n.a.	V1.5.15.131b
CP676	A0	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.90.0.975	n.a.	n.a.
CP676	B1	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	V1.91.0	1.1.1	n.a.
CP676	C1	1SAP576100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.0	1.2	n.a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.0.1.243	1.2.3	n.a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.4.0.89	2.0.0/2.0.1 2.0.2	n.a.
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.0.351	2.0.3/2.0.4 2.1.0/2.1.1	n.a.

Product	Index	Order code	Product line	Operating system (OS)	BSP	PB610	Autom. Builder	Micro-browser
CP676	C3	1SAP676100R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	V2.6.1.175	2.1.2	n.a.
CP676-WEB	A0	1SAP576200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.76	n.a.	n.a.	V1.5.15.131b
CP676-WEB	C1	1SAP576200R0001	CP600	Win Embedd. CE 6.0 Core	UN30, V1.96	n.a.	1.2	V1.5.15.131b
CP6605	A0	1SAP560510R0001	CP600-Pro	Linux 3.12	UN70, V1.0.298	V2.6.1.126	n.a.	n.a.
CP6605	A0	1SAP560510R0001	CP600-Pro	Linux 3.12	UN70, V1.0.298	V2.6.1.175	2.1.2	n.a.
CP6607	A0	1SAP560710R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.126	n.a.	n.a.
CP6607	A0	1SAP560710R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.175	2.1.2	n.a.
CP6610	A0	1SAP561010R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.126	n.a.	n.a.
CP6610	A0	1SAP561010R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.175	2.1.2	n.a.
CP6615	A0	1SAP561510R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.126	n.a.	n.a.
CP6615	A0	1SAP561510R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.175	2.1.2	n.a.
CP6621	A0	1SAP562110R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.126	n.a.	n.a.
CP6621	A0	1SAP562110R0001	CP600-Pro	Linux 3.12	UN65, V1.0.304	V2.6.1.175	2.1.2	n.a.

ABB Automation Products GmbH
Eppelheimer Straße 82
D-69123 Heidelberg / Germany
Tel.: +49 62 21 701 1444
Fax: +49 62 21 701 1382

abb.com/plc

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.
Copyright© 2018 ABB
All rights reserved

3ADR059112K0201, REV C, en_US, 13 September 2018