


# FurseWELD

## Bar to steel surface BS3



**Bar to steel surface BS3 - FurseWELD**

Flat tape conductor size A (mm)	Part no.				
	Powder cartridge	Standard mould	Handle clamp	Mini mould	Mini handle clamp
20 x 3	90P10	BS3-4-203	HCPK4	BS3-3-203	HCPK3
25 x 3	115P10	BS3-4-253	HCPK4	BS3-3-253	HCPK3
25 x 4	115P10	BS3-4-254	HCPK4	BS3-3-254	HCPK3
25 x 6	150P10	BS3-4-256	HCPK4	—	—
30 x 2	115P10	BS3-4-302	HCPK4	BS3-3-302	HCPK3
30 x 3	115P10	BS3-4-303	HCPK4	BS3-3-303	HCPK3
30 x 4	150P10	BS3-4-304	HCPK4	—	—
30 x 5	200P10	BS3-4-305	HCPK4	—	—
31 x 3	115P10	BS3-4-313	HCPK4	BS3-3-313	HCPK3
31 x 6	200P10	BS3-4-316	HCPK4	—	—
38 x 3	150P10	BS3-4-383	HCPK4	—	—
38 x 5	200P10	BS3-4-385	HCPK4	—	—
38 x 6	250P10	BS3-4-386	HCPK4	—	—
40 x 3	150P10	BS3-4-403	HCPK4	—	—
40 x 4	200P10	BS3-4-404	HCPK4	—	—
40 x 5	250P10	BS3-4-405	HCPK4	—	—
40 x 6	250P10	BS3-4-406	HCPK4	—	—
50 x 3	250P10	BS3-4-503	HCPK4	—	—
50 x 4	250P10	BS3-4-504	HCPK4	—	—
50 x 5	250P10	BS3-4-505	HCPK4	—	—
50 x 6	250P10	BS3-4-506	HCPK4	—	—

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request