


Molded Case Circuit Breakers with Thermal-Magnetic Trip Unit

DES031

Record PlusTM Types FC & FB
Let-Through Energy Curves

FC Voltage Ratings
2– and 3–pole – 600/347 Vac, 500 Vdc

FB Voltage Ratings
2– and 3–pole – 600/347
Vac 1–pole – 347 Vax

Frequency Rating
50/60 Hertz

Current Ratings
15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 80, 90, 100 Amperes

1SQC930047D0201, DES031 February 2023 Rev. B