

REV.	ECN NO.	APPD.
-		

BACK VIEW

438

400.4

350

319


288

31.3



86.2

47.4

40.6



Tolerances standard (Sheet metal)				
DIMENSION	GRADE			
	I	II	III	IV
0.5<L<3	±0.05	±0.1	±0.2	--
3<L<6	±0.05	±0.1	±0.3	±0.5
6<L<30	±0.1	±0.2	±0.5	±1.0
30<L<120	±0.15	±0.3	±0.8	±1.5
120<L<400	±0.2	±0.5	±1.2	±2.5
400<L<1000	±0.3	±0.8	±2.0	±4.0
1000<L<2000	±0.5	±0.12	±3.0	±6
>2000	--	±2.0	±4.0	±8.0
TOLEANCE GRADE	II			
A0.4/0.0 2.5/0.000 0.0/0.0; ±0.5'				

X.	X.		PART NO. V20200515-014-04					
.X	.X		TITLE: UPS PowerValue 11RT G2 3 kVA B UL-Back View					
.XX	.XX		UNIT: MILIMETER					
			MAT'L		DWG NO.			
			FINISH: SEE SPEC DESCRIPTION		APPRD:	DATE:		
					CHECK:	DATE:		
			DESIGN:		DATE:	PAPER SCALE	SHEET	REV
						1:1	1/1	A