


REV.	ECN NO.	APPD.
-		

BACK VIEW



Tolerances standard (Sheetmetal)				
DIMENSION	GRADE			
	I	II	III	IV
0.5<L<3	± 0.05	± 0.1	± 0.2	--
3<L<6	± 0.05	± 0.1	± 0.3	± 0.5
6<L<30	± 0.1	± 0.2	± 0.5	± 1.0
30<L<120	± 0.15	± 0.3	± 0.8	± 1.5
120<L<400	± 0.2	± 0.5	± 1.2	± 2.5
400<L<1000	± 0.3	± 0.8	± 2.0	± 4.0
1000<L<2000	± 0.5	± 0.12	± 3.0	± 6
>2000	--	± 2.0	± 4.0	± 8.0
TOLERANCE GRADE	II			
A0/00 0/00 0/00 0/00 0/00; ± 0.5'				

X.	X.		PART NO. V20200515-013-05						
.X	.X		TITLE: External battery module 11RT G2 2-3 kVA UL-Back View						
.XX	.XX								
		UNIT: MILIMETER	APPRD:		DATE:		DWG NO.		
		MAT'L							
		FINISH: SEE SPEC DESCRIPTION	DESIGN:		DATE:		PAPER SCALE 1:1	SHEET 1/1	REV A