





REV.	ECN NO.	APPD.
-		

FRONT VIEW



Tolerances standard (Sheetmetal)				
DIMENSION	GRADE			
	I	II	III	IV
0.5<L<3	±0.05	±0.1	±0.2	--
3<L≤6	±0.05	±0.1	±0.3	±0.5
6<L≤30	±0.1	±0.2	±0.5	±1.0
30<L≤120	±0.15	±0.3	±0.8	±1.5
120<L≤400	±0.2	±0.5	±1.2	±2.5
400<L≤1000	±0.3	±0.8	±2.0	±4.0
1000<L≤2000	±0.5	±0.12	±3.0	±6
>2000	--	±2.0	±4.0	±8.0
TOLERANCE GRADE	II			
A B C D E F G H I J K L M N O P Q R S T U V W X Y Z ±0.5'				

X.	X.		PART NO. V20200515-011-06				
.X	.X						
.XX	.XX	UNIT: MILIMETER	TITLE: UPS PowerValue 11RT G2 1 kVA B UL- Front View Without Front Panel		DWG NO.		
			APPRD:	DATE:			
			CHECK:	DATE:			
				FINISH: SEE SPEC DESCRIPTION	DESIGN:	DATE:	PAPER SCALE
					1:1	1/1	A