


REV.	ECN NO.	APPD.
-		

BACK VIEW



Tolerances standard (Sheetmetal)				
DIMENSION	GRADE			
	I	II	III	IV
0.5<L<3	±0.05	±0.1	±0.2	--
3<L<6	±0.05	±0.1	±0.3	±0.5
6<L<30	±0.1	±0.2	±0.5	±1.0
30<L<120	±0.15	±0.3	±0.8	±1.5
120<L<400	±0.2	±0.5	±1.2	±2.5
400<L<1000	±0.3	±0.8	±2.0	±4.0
1000<L<2000	±0.5	±0.12	±3.0	±6
>2000	--	±2.0	±4.0	±8.0
TOLERANCE GRADE		II		
A0.4/0.0 2.0/0.000.0/0.0; ±0.5'				

X.	X.		PART NO. V20200515-012-08				
.X	.X		TITLE: UPS PowerValue 11RT G2 1.5 kVA B UL-Back View				
.XX	.XX	UNIT: MILIMETER	APPRD:		DWG NO.		
		MAT'L	CHECK:		PAPER SCALE		
			DESIGN:		SHEET		
		FINISH: SEE SPEC DESCRIPTION	DATE:		REV		
					A		