

REV.	ECN NO.	APPD.
-		

BACK VIEW

438

383.9

352.9

321.9

290.9

29.5


52.1



86.2

29.1

59.1

Tolerances standard (Sheetmetal)				
DIMENSION	GRADE			
	I	II	III	IV
0.5<L<3	±0.05	±0.1	±0.2	--
3<L<6	±0.05	±0.1	±0.3	±0.5
6<L<30	±0.1	±0.2	±0.5	±1.0
30<L<120	±0.15	±0.3	±0.8	±1.5
120<L<400	±0.2	±0.5	±1.2	±2.5
400<L<1000	±0.3	±0.8	±2.0	±4.0
1000<L<2000	±0.5	±0.12	±3.0	±6
>2000	--	±2.0	±4.0	±8.0
TOLENCE GRADE	II			
A B C D E F G H I J K L M N O P Q R S T U V W X Y Z; ±0.5'				

X.	X.		PART NO.	
.X	.X		V20200515-013-08	
.XX	.XX		TITLE: UPS PowerValue 11RT G2 2 kVA B UL-Back View	
		UNIT: MILIMETER	APPD:	
		MAT'L	DATE:	
		FINISH: SEE SPEC DESCRIPTION	DATE:	

		PART NO. V20200515-013-08						
UNIT: MILIMETER		TITLE: UPS PowerValue 11RT G2 2 kVA B UL-Back View						
MAT'L		APPRD:					DATE:	
FINISH:		CHECK:		DATE:		DWG NO.		
SEE SPEC DESCRIPTION		DESIGN:		DATE:		PAPER SCALE	SHEET	REV
						1:1	1/1	A