


Movion®

Where modularity leads to simplicity

- Modular luminaires with multiple mounting options
- Easy, quick installation and maintenance due to smart features
- Excellent lighting distribution and visibility

Movion®

Modular & versatile



Escape route lighting - Recessed

- Round shaped design fitting any ceiling
- Specially designed lens for optimal light distribution - long and wide beam
- Quick installation and parallel wiring option with the smart loop-in, loop-out system


Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Light optics	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
511013121/50	EL800R-M3/ST ER	230-240 AC 50/60Hz	1 x LED 1W	101	Escape route	3.33 / 3.19	3	5-35	0.31
511013221/50	EL800R-M3/DALI ER	230-240 AC 50/60Hz		101		3.33 / 3.19	3	5-35	0.31
511013321/50	EL800R-M3/COM ER	230-240 AC 50/60Hz		101		3.33 / 3.19	3	5-35	0.31
511012821/50	EL800R-230 ER	220-240 AC/DC 0-60Hz		124		3.21 / 3.05	230V	0-40	0.21
511012721/50	EL800R-230/FLX ER	220-240 AC/DC 0-60Hz		124		3.21 / 3.05	230V	0-40	0.21
511012621/50	EL800R-230/LTC ER	220-240 AC 50/60Hz		124		3.21 / 3.05	230V	0-40	0.21
511013122/50	EL800R-M3/ST OA	230-240 AC 50/60Hz		109	Open area	3.33 / 3.19	3	5-35	0.31
511013222/50	EL800R-M3/DALI OA	230-240 AC 50/60Hz		109		3.33 / 3.19	3	5-35	0.31
511013322/50	EL800R-M3/COM OA	230-240 AC 50/60Hz		109		3.33 / 3.19	3	5-35	0.31
511012822/50	EL800R-230 OA	220-240 AC/DC 0-60Hz		134		3.21 / 3.05	230V	0-40	0.21
511012722/50	EL800R-230/FLX OA	220-240 AC/DC 0-60Hz		134		3.21 / 3.05	230V	0-40	0.21
511012622/50	EL800R-230/LTC OA	220-240 AC 50/60Hz		134		3.21 / 3.05	230V	0-40	0.21

Accessories

Order code	Description	Product type
11160111/50	RENO 2200-3300	Renovation kit recess mounted, white

IP Rating	Product type
IP20	flush mount from above
IP42	flush mount from below



Movion®

Modular & versatile



Escape route lighting - Surface mount

- Square shaped design fitting any ceiling
- Specially designed lens for optimal light distribution - long and wide beam
- Quick installation and parallel wiring option with the smart loop-in, loop-out system
- Light track mountable with 3C adapter included

Luminaire


Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Light optics	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
511013111/50	EL800S-M3/ST ER	230-240 AC 50/60Hz	1 x LED 1W	101	Escape route	3.33 / 3.19	3	5-35	0.39
511013211/50	EL800S-M3/DALI ER	230-240 AC 50/60Hz		101		3.33 / 3.19	3	5-35	0.39
511013311/50	EL800S-M3/COM ER	230-240 AC 50/60Hz		101		3.33 / 3.19	3	5-35	0.39
511012811/50	EL800S-230 ER	220-240 AC/DC 0-60Hz		124		3.21 / 3.05	230V	0-40	0.29
511012711/50	EL800S-230/FLX ER	220-240 AC/DC 0-60Hz		124		3.21 / 3.05	230V	0-40	0.29
511012611/50	EL800S-230/LTC ER	220-240 AC 50/60Hz		124		3.21 / 3.05	230V	0-40	0.29
511013112/50	EL800S-M3/ST OA	230-240 AC 50/60Hz		109	Open area	3.33 / 3.19	3	5-35	0.39
511013212/50	EL800S-M3/DALI OA	230-240 AC 50/60Hz		109		3.33 / 3.19	3	5-35	0.39
511013312/50	EL800S-M3/COM OA	230-240 AC 50/60Hz		109		3.33 / 3.19	3	5-35	0.39
511012812/50	EL800S-230 OA	220-240 AC/DC 0-60Hz		134		3.21 / 3.05	230V	0-40	0.29
511012712/50	EL800S-230/FLX OA	220-240 AC/DC 0-60Hz		134		3.21 / 3.05	230V	0-40	0.29
511012612/50	EL800S-230/LTC OA	220-240 AC 50/60Hz		134		3.21 / 3.05	230V	0-40	0.29



Accessories

Order code	Description	Product type
5110007/50	PK EL800	Pendant kit surface mounted escape

Modular pendant tubes and accessories to be used in combination with the pendant kit see page XX.



Movion®

Modular & versatile





Escape route signalisation - 22m

- One version available for wall and ceiling mount
- Strong light distribution with 500 cd/m²
- Light track mountable with 3C adapter included
- Recess kit for flush mounting available

Luminaire

Order code	Description	Input voltage	Lamp type	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
411013111/50	XT800S-M3/ST 22M	230-240 AC 50/60Hz	1 x LED 2W	4.38 / 4.14	3	5-35	0.53
411013211/50	XT800S-M3/DALI 22M	230-240 AC 50/60Hz		4.38 / 4.14	3	5-35	0.53
411013311/50	XT800S-M3/COM 22M	230-240 AC 50/60Hz		4.38 / 4.14	3	5-35	0.53
411013411/50	XT800S-M3/BT 22M	230-240 AC 50/60Hz		4.38 / 4.14	3	5-35	0.53
411012811/50	XT800S-230 22M	220-240 AC/DC 0-60Hz		4.04 / 3.82	230V	0-40	0.48
411012711/50	XT800S-230/FLX 22M	220-240 AC/DC 0-60Hz		4.04 / 3.82	230V	0-40	0.48
411012611/50	XT800S-230/LTC 22M	220-240 AC 50/60Hz		4.04 / 3.82	230V	0-40	0.48

Legends

Part No.	Legends
1522251/50	
1522252/50	
1522253/50	
1522258/50	
1522250/50	
1522210/50	
1522211/50	


IP Rating	Product type
IP20*	flush mount from above
IP42*	flush mount from below


*Only applicable when the recess kit is used.

Accessories

Order code	Description	Product type
4110001/50	RK XT800	Recess kit for exit signs
4110003/50	PK XT800*	Pendant kit surface mounted exit
4100007/50	RENO XT800**	Renovation kit for exit signs

*Modular pendant tubes and accessories to be used in combination with the pendant kit see page XX.
** Use the RENO XT800 in combination with RK XT800.





Movion®


Modular & versatile





Hybrid - 22m

- All-in-one escape route lighting and signalisation luminaire for wall and ceiling mount
- Available lenses for escape route lighting and 5 lux illumination of safety equipment
- Light track mountable with 3C adapter included
- Recess kit for flush mounting available



Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
411113111/50	XTH800S-M3/ST 22M	230-240 AC 50/60Hz	1 x LED 2W + 1 x LED 1W	67	5.02 / 4.89	3	5-35	0.6
411113211/50	XTH800S-M3/DALI 22M	230-240 AC 50/60Hz		67	5.02 / 4.89	3	5-35	0.6
411113311/50	XTH800S-M3/COM 22M	230-240 AC 50/60Hz		67	5.02 / 4.89	3	5-35	0.6
411112811/50	XTH800S-230 22M	220-240 AC/DC 0-60Hz		82	4.97 / 4.74	230V	0-40	0.5
411112711/50	XTH800S-230/FLX 22M	220-240 AC/DC 0-60Hz		82	4.97 / 4.74	230V	0-40	0.5
411112611/50	XTH800S-230/LTC 22M	220-240 AC 50/60Hz		82	4.97 / 4.74	230V	0-40	0.5

Legends

Part No.	Legends
1522251/50	
1522252/50	
1522253/50	
1522258/50	
1522250/50	
1522210/50	
1522211/50	

Accessories

Order code	Description	Product type
4110001/50	RK XT800	Recess kit for exit signs
4110003/50	PK XT800*	Pendant kit surface mounted exit
4110004/50	WB XTH 800	Wall bracket for Hybrid exit signs
4100007/50	RENO XT800**	Renovation kit for exit signs

*Modular pendant tubes and accessories to be used in combination with the pendant kit see page XX.
** Use the RENO XT800 in combination with RK XT800.

IP Rating	Product type
IP20*	flush mount from above
IP42*	flush mount from below

*Only applicable when the recess kit is used.

