

## CMPS-E Series

Thermoplastic pictogram sign




### Features

- Energy efficient, long-life white LEDs consuming 1.5W at normal operation
- 120/277/347VAC, 6-24VDC input
- Universal single and double face
- Automatic, temperature compensated, pulse type charger
- Low voltage disconnect prevents over discharge of battery
- Automatic brownout protection
- Battery lock-out prevents discharge during installation
- Comes standard with three pictogram legends for direction selection
- Red LED charger monitor
- Injection-molded off-white thermoplastic ABS housing
- Fast and easy installation with snap-together design
- Ceiling, wall or end mount installation
- CSA C22.2 no.141-10 listed
- Selection of self-powered using a 3.6V Ni-Cd battery and AC/DC model
- **Warranty details at: [www.emergi-lite.ca/](http://www.emergi-lite.ca/)**



### Dimensions

Dimensions are approximate and subject to change.



### Power consumption and unit rating

Series	Model	Wattage	Current	AC specs		DC specs
					Efficiency	
CM-PS	AC/DC	120V, 50/60 Hz	1.5W	0.01A	0.96PF	6-24VDC-1W
		277V, 50/60 Hz	2W	0.01A	0.92PF	
		347V, 50/60 Hz	2.4W	0.01A	0.91PF	
	Self-powered	120V, 50/60 Hz	2.5W	0.24A	0.98PF	
		277V, 50/60 Hz	3W	0.014A	0.93PF	
		347V, 50/60 Hz	3.5W	0.017A	0.92PF	

### Ordering information

Series	Voltage	Brand
CM-PS	-ACDC= 120/277/347VAC, 6-24VDC -SP= 120/277/347VAC, self-powered (120 mins.)	-E= Emergi-Lite®

Example: CM-PS-ACDC-E