中国国家强制性产品认证证书

证书编号：2015010303819793

委托人名称、地址

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

生产者（制造商）名称、地址

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称、地址

ABB STOTZ-KONTAKT GmbH

Hauptstrasse 14-16, D-78132 Hornberg, Germany

产品名称和系列、规格、型号

继电器

CM-ENS.xxx:
Ui:300V;Uimp:4kV;Ithe:4A;AC-15:Ue/Ie:AC230V/3A;DC-13:Ue/Ie:DC24V/2A;IP20；型号解释见附件

产品标准和技术要求

GB/T14048.5-2017

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，特发此证。

发证日期：2019 年 01 月 14 日　　有效期至：2020 年 11 月 10 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2015 年 11 月 10 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

主　任：

中国质量认证中心

Q 2190799

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2015010303819793

NAME AND ADDRESS OF THE APPLICANT

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE FACTORY

ABB STOTZ-KONTAKT GmbH

Hauptstrasse 14-16, D-78132 Hornberg,Germany

PRODUCT NAME, MODEL AND SPECIFICATION

Relay

CM-ENS.xxx：Ui:300V;Uimp:4kV;Ithe:4A;AC-15:Ue/Ie:AC230V/3A;DC-13:Ue/Ie:DC24V/2A;IP20

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.5-2017

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Jan.14,2019 **Valid until:** Nov.10,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Nov.10,2015

The certificate information is available through CNCA's website: www.cnca.gov.cn

President:

Lu Mei

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China Tel: +86 10 83886666

Q 2190799

中国国家强制性产品认证证书

附　　录

证书编号：2015010303819793

纸　号：2190799

型号解释：

CM- ENS .□□ S

I II III

I	Series 系列	CM-	Electronic measuring and monitoring relay 电子测量与监视继电器	
II	Variant 种类	ENS	Liquid Level Monitoring Relay 液位监视继电器	AC15: 230Vac , 3A
III	.□□	11	Supply Voltage 控制电源电压	
	Terminal 接线端子 形式	S	Screw pressure terminal 螺钉连接端子	DC13: 24Vdc , 2A
		P	Push-in spring force terminal 插入式弹簧连接端子	Ithe : 4A

Type	Supply Voltage
CM-ENS.11S	24-240V AC/DC 50/60Hz
CM-ENS.11P	24-240V AC/DC 50/60Hz
CM-ENS.13S	110-130V / 220-240V AC 50/60Hz
CM-ENS.13P	110-130V / 220-240V AC 50/60Hz
CM-ENS.21S	24-240V AC/DC 50/60Hz
CM-ENS.21P	24-240V AC/DC 50/60Hz
CM-ENS.23S	110-130V / 220-240V AC 50/60Hz
CM-ENS.23P	110-130V / 220-240V AC 50/60Hz
CM-ENS.31S	24-240V AC/DC 50/60Hz
CM-ENS.31P	24-240V AC/DC 50/60Hz

注：此附录与证书同时使用时有效。

主　任：

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

中国质量认证中心