产品认证证书

证书编号：CQC2008010302317034

申请人名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

制造商名称及地址

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

生产企业名称及地址

ABB Oy (V054902)

Muottitie 2A FI-65320 VAASA, Finland

产品名称和系列、规格、型号

隔离开关

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT;具体规格见附件

产品标准和技术要求

GB/T 14048.3-2017

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462141-2019 认证规则的要求，特发此证。

发证日期：2020 年 10 月 29 日　　有效期至：2025 年 10 月 29 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2020 年 09 月 02 日

主任：

中国质量认证中心

中国．北京．南四环西路 188 号 9 区 100070

http://www.cqc.com.cn

C 0176514

PRODUCT CERTIFICATE

CERTIFICATE NO.: CQC2008010302317034

NAME AND ADDRESS OF THE APPLICANT

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE MANUFACTURER

ABB Oy

Muottitie 2A FI-65320 VAASA, Finland

NAME AND ADDRESS OF THE FACTORY

ABB Oy (V054902)

Muottitie 2A FI-65320 VAASA, Finland

PRODUCT NAME, MODEL AND SPECIFICATION

Switch-disconnector

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT;see the appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T 14048.3-2017

TYPE OF CERTIFICATION SCHEMES

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462141-2019 .

Valid from: Oct.29,2020 **Valid until:** Oct.29,2025

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Sep.02,2020

President: _____

Lu Mei

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

Section 9,No.188,Nansihuan Xilu, Beijing 100070 P.R.China

http://www.cqc.com.cn

C 0176514

产品认证证书

附　　录　　第 1 页 共 3 页

证书编号：CQC2008010302317034　　纸　号：176514

OT45ML, OT63F, OT63FT, OT63ML, OT80F, OT80FT
Uimp: 8kV;
Ui: 750V;
OT45ML:
Ith: 63A
Ue/Ie: 415/440/500V/63A(AC-21A, AC-22A)
415/440V/63A, 500V/45A(AC-23A)
OT63F, OT63FT:
Ith: 63A
Ue/Ie: 415/440/500/690V/63A(AC-21A, AC-22A)
415/440V/63A, 500V/45A, 690V/20A(AC-23A)
OT63ML, OT80F, OT80FT:
Ith: 80A
Ue/Ie: 415/440/500/690V/80A(AC-21A, AC-22A)
415V/75A, 440V/65A, 500V/58A, 690V/20A(AC-23A)
Icm(峰值): 2115A;
Icw: 1.5kA/1s;
Iq: OT45ML:500V/100kA;
OT63F, OT63FT, OT63ML, OT80F, OT80FT:500V/100kA;690V/50kA;
使用类别: AC-21A, AC-22A, AC-23A;
极数: 3P, 4P;
适用频率: 50/60Hz;
IP20(仅对前面板)

注：此附录与证书同时使用时有效。

主任：

中国质量认证中心

中国．北京．南四环西路 188 号 9 区 100070
http://www.cqc.com.cn

产品认证证书

附　　录　　第 2 页 共 3 页

证书编号：CQC2008010302317034　　纸　号：176514

型号解释：

注：此附录与证书同时使用时有效。

主任：

中国质量认证中心


中国．北京．南四环西路 188 号 9 区 100070

http://www.cqc.com.cn

产品认证证书

附　　录　　第 3 页 共 3 页

证书编号：CQC2008010302317034　　纸　号：176514



注：此附录与证书同时使用时有效。

主任：

中国质量认证中心

中国．北京．南四环西路 188 号 9 区 100070
http://www.cqc.com.cn