产品认证证书

II型自愿认证

证书编号：CQC2008010309289461

发证日期：2021年10月09日

有效期至：2031年10月09日

委托人名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称及注册地址	ABB新会低压开关有限公司 广东省江门市新会区今古洲工业开发区
生产企业名称及生产地址	ABB新会低压开关有限公司 广东省江门市新会区今古洲工业开发区
产品名称和系列、规格、型号	接触器 A50，A63，A75；规格参数详见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 签发

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0110796

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2008010309289461

Valid from: Oct.09,2021

Valid until: Oct.09,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Contactor A50 , A63 , A75 ; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 刘[illegible]

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

http://www.cqc.com.cn Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China Tel: +86 10 83886666

C(2) 0110796

产品认证证书

II型自愿认证

证书编号：CQC2008010309289461

本证书及附件应同时使用，信息查验说明见证书页

纸号：110796

上报参数：

A50，A63，A75

Ui:1000V;

Uimp:8kV;

A50:Ith:100A;

Ue/Ie: 220-230-240V/53A,380-400V/50A,415V/50A,440V/45A,
500V/45A,690V/35A,1000V/23A(AC-3);

Ue/Ie:400V/63A(AC-8a);Ue/Ie:690V/100A(AC-1);

A63:Ith:125A

Ue/Ie: 220-230-240V/65A,380-400V/65A,415V/65A,440V/65A,
500V/55A,690V/43A,1000V/25A(AC-3);

Ue/Ie:400V/85A(AC-8a);Ue/Ie:690V/115A(AC-1);

A75:Ith:125A;

Ue/Ie: 220-230-240V/75A,380-400V/75A,415V/75A,440V/70A,
500V/65A,690V/46A,1000V/28A(AC-3);

Ue/Ie:400V/95A(AC-8a);Ue/Ie:690V/125A(AC-1);

使用类别:AC-1,AC-3,AC-8a;

3P

Us:24V 50Hz/60Hz,42V 50Hz/60Hz,48V 50Hz/60Hz,110V 50Hz/110~120V 60Hz,
190V 50Hz/220V 60Hz,220~230V 50Hz/230~240V 60Hz,230~240V 50Hz/240~260V 60Hz,
380~400V 50Hz/400~415V 60Hz,400~415V 50Hz/415~440V 60Hz;

IP20(线圈),IP10(端子);

配用的辅助触头(外置)：

CAL5，证书编号：CQC2004010305133985;

1NO1NC;

Ith:16A;

AC-15：Ue/Ie: 24~127V/6A, 220~240V/4A, 380~440V/3A, 500~690V/2A;

DC-13：Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 110V/0.55A, 125V/0.55A, 220V/0.3A, 250V/0.3A;

中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2008010309289461

本证书及附件应同时使用，信息查验说明见证书页

纸号：110796

型号解释：

A5030-1 1

- 附件种类数量：空白或 00:没有附加附件; 11:附加一只附件 CAL5;
- 常闭主触点对数 0：0 对常闭主触点
- 常开主触点对数 3：3 对常开主触点
- 380V, AC3 应用类别下额定工作电流 ： 50:50A, 63:65A, 75:75A,
- 系列名称：A 系列接触器

中国质量认证中心