产品认证证书

II型自愿认证

证书编号：CQC2013010304646598

发证日期：2021年10月09日

有效期至：2031年10月09日

委托人名称及注册地址	ABB Electrification Sweden AB, Motor Starting & Safety Motorgrand 20, 72161 Vasteras, Sweden
制造商名称及注册地址	ABB Electrification Sweden AB, Motor Starting & Safety Motorgrand 20, 72161 Vasteras, Sweden
生产企业名称及生产地址	ABB新会低压开关有限公司 广东省江门市新会区今古洲工业开发区
产品名称和系列、规格、型号	接触器 AX185-30-□□-□□、AX205-30-□□-□□；规格参数详见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 刘[illegible]　签发 谢肇煦

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0110800

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2013010304646598

Valid from: Oct.09,2021

Valid until: Oct.09,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB Electrification Sweden AB, Motor Starting & Safety Motorgrand 20, 72161 Vasteras, Sweden
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB Electrification Sweden AB, Motor Starting & Safety Motorgrand 20, 72161 Vasteras, Sweden
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Contactor AX185-30-□□-□□、AX205-30-□□-□□; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 刘[illegible]

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

http://www.cqc.com.cn Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China Tel: +86 10 83886666

C(2) 0110800

产品认证证书

II型自愿认证

证书编号：CQC20130103046465 98

本证书及附件应同时使用，信息查验说明见证书页

纸号：110800

型号：AX185-30-□□-□□、AX205-30-□□-□□；I_{th}：AX185：250A，AX205：275A；U_i：1000V；U_{imp}=8kV；

U_s：

频率	U_s(V～)							
50Hz	24	48	110	190	220-230	230-240	380-400	400-415
60Hz	24	48	110-120	220	230-240	240-260	400-415	415-440

极数：3P；使用类别、U_e、I_e：

使用类别	U_e(V～)	I_e(A)	
		AX185	AX205
AC-1	690	250	275
AC-3	220-230-240	185	205
AC-3	380-400	185	205
AC-3	415	185	205
AC-3	440	145	185
AC-3	500	145	170
AC-3	690	120	170

配用的辅助触头：2NO2NC（最多配置）

型号：CAL18-11 或 CAL18X-11；I_{th}：16A；使用类别、U_e、I_e：

	AC-15	DC-13

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC20130103046465598

本证书及附件应同时使用，信息查验说明见证书页

纸号：110800

I_e/A	6	4	3	2	6	2.8	1	0.55	0.3
U_e/V(CAL18-11)	127	230/240	400/440	500/690	24	48	72	125	250
U_e/V(CAL18X-11)	24～127	220～240	380～440	500～690	24	48	72	125	250

型号的解释：

AX□□- 30-□□-□□

控制线圈型号代码：见表一

附件种类数量：00-没有附加附件；11-附加一只附件 CAL18-11 或 CAL18X-11；22-附加两只附件 CAL18-11 或 CAL18X-11

常闭主触点对数 0：0 对常闭主触点

常开主触点对数 3：3 对常开主触点

380V 工作电压, AC-3 下额定工作电流(A)
185:185A, 205:205A;

系列名称： AX 系列接触器

中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2013010304646598

本证书及附件应同时使用，信息查验说明见证书页

纸号：110800

表一

额定工作电压（Vac）		线圈代号
50Hz	60Hz	
24	24	81
48	48	83
110	110-120	84
220-230	230-240	80
230-240	240-260	88
380-400	400-415	85
400-415	415-440	86
190	220	36

CQC 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心