产品认证证书

II型自愿认证

证书编号：CQC2014010307677590

发证日期：2022年03月30日

有效期至：2032年03月29日

委托人名称及注册地址	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
制造商名称及注册地址	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
生产企业名称及生产地址	ABB S.P.A. - ABB SACE Division Via Enrico Fermi,14 - 03100 Frosinone Italy
产品名称和系列、规格、型号	万能式断路器 E2.2B, E2.2N, E2.2S, E2.2H, E2.2H/E, E2.2H/E9, E2.2S/E9, E2.2B-A, E2.2N-A, E2.2S-A, E2.2H-A, E2.2V-A;详见附件
产品标准和技术要求	GB/T 14048.2-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020 年 09 月 02 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 签发

中国质量认证中心

C(2) 0147817

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2014010307677590

Valid from: Mar.30,2022

Valid until: Mar.29,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB S.P.A. Via Pescaria n°5, 24123 Bergamo Italy
NAME AND LOCATION OF THE FACTORY	ABB S.P.A. - ABB SACE Division Via Enrico Fermi,14 - 03100 Frosinone Italy
PRODUCT NAME, MODEL AND SPECIFICATION	Air circuit breaker E2.2B, E2.2N, E2.2S, E2.2H, E2.2H/E, E2.2H/E9, E2.2S/E9, E2.2B-A, E2.2N-A, E2.2S-A, E2.2H-A, E2.2V-A;See the appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.2-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Sep.02,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 陈昕

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心 CHINA QUALITY CERTIFICATION CENTRE

C(2) 0147817

产品认证证书

II型自愿认证

证书编号：CQC2014010307677590

本证书及附件应同时使用，信息查验说明见证书页

纸号：147817

E2.2B, E2.2N, E2.2S, E2.2H, E2.2H/E, E2.2H/E9, E2.2S/E9,
E2.2B-A, E2.2N-A, E2.2S-A, E2.2H-A, E2.2V-A：
Uimp: 12kV;
Ui: 1000V, 1500V(E2.2H/E, E2.2H/E9);
Ue: AC220V, AC230V, AC380V, AC400V, AC415V, AC440V, AC500V,
AC525V, AC660V, AC690V,
AC800V/AC900V(E2.2S/E, E2.2H/E9), AC1000/1140V(E2.2H/E);
In: 400A, 600A, 630A, 800A, 1000A, 1200A, 1250A, 1600A, 2000A,
2500A(E2.2B, E2.2N, E2.2S,
E2.2H, E2.2H/E, E2.2H/E9, E2.2S/E9);
250A, 400A, 600A, 630A, 800A, 1000A, 1200A, 1600A(E2.2B-A);
250A, 400A, 600A, 630A, 800A, 1000A, 1200A, 1600A, 2000A(E2.2N-A,
E2.2S-A, E2.2H-A,
E2.2V-A);
过电流脱扣器类型: 电子式;
Ics, Icu 和 Icw 见下表:

		E2.2B	E2.2N	E2.2S	E2.2H	E2.2S/E9	E2.2H/E9	E2.2H/E	E2.2B-A	E2.2N-A	E2.2S-A	E2.2H-A	E2.2V-A
Icu 220/230/380/400/415Vac	[kA]	42	66	85	100	-	-	-	42	50	66	85	100
Icu 440Vac	[kA]	42	66	85	100	-	-	-	42	50	66	85	100
Icu 500/525Vac	[kA]	42	66	66	85	-	-	-	42	50	66	85	85
Icu 660/690Vac	[kA]	42	66	66	85	-	-	-	42	50	66	85	85
Icu 800Vac	[kA]	-	-	-	-	50	65		-	-	-	-	-
Icu 900Vac	[kA]	-	-	-	-	50	65		-	-	-	-	-
Icu 1000-1140Vac	[kA]	-	-	-	-	-	-	50	-	-	-	-	-
Ics 220/230/380/400/415Vac	[kA]	42	66	85	100	-	-	-	42	50	66	85	100
Ics 440Vac	[kA]	42	66	85	100	-	-	-	42	50	66	85	100
Ics 500/525Vac	[kA]	42	66	66	85	-	-	-	42	50	66	85	85
Ics 660/690Vac	[kA]	42	66	66	85	-	-	-	42	50	66	85	85
Ics 800Vac	[kA]	-	-	-	-	50	65		-	-	-	-	-
Ics 900Vac	[kA]	-	-	-	-	50	65		-	-	-	-	-
Ics 1000-1140Vac	[kA]	-	-	-	-	-	-	50	-	-	-	-	-
Icw 1s 690Vac	[kA]	42	66	66	85	-	-	-	42	50	66	85	85
Icw 1s 800-900Vac	[kA]	-	-	-	-	50	65	-	-	-	-	-	-
Icw 1s 1000-1140Vac	[kA]	-	-	-	-	-	-	50	-	-	-	-	-

适用频率: 50/60Hz; 适用隔离
选择性类别: B; 极数: 3P, 4P;

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CQC 中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2014010307677590

本证书及附件应同时使用，信息查验说明见证书页

纸号：147817

辅助触头(CQC 证书编号: CQC21107322161): KW-7
2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC Ith: 16A
AC-12：Ue/Ie：AC250V/16A、AC125V/16A、AC250V/10A、AC125V/10A、AC250V/8A、
AC125V/8A、AC250V/6A、AC125V/6A、AC400V/3A；
DC-12：Ue/Ie：DC250V/0.3A、DC125V/0.6A；
辅助触头(本体): 2NO2NC, 4NO4NC, 6NO6NC, 15NO15NC Ith: 16A
AC-12: Ue/Ie: 400V/3A;
AC-14: Ue/Ie: 400V/3A, 250V/10A;
DC-12: Ue/Ie: 24V/0.1A;
DC-13: Ue/Ie: 250V/0.15A;125V/0.3A;
符合附录 N 的电子附件:
闭合线圈：YC: Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC,
120-127 VAC/DC, 220-240 VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500
VAC; 50/60Hz
欠压脱扣器：YU: Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC,
120-127 VAC/DC, 220-240 VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500
VAC; 50/60Hz
分励脱扣器：YO: Us: 24VAC/DC, 30 VAC/DC, 48 VAC/DC, 60 VAC/DC, 110-120 VAC/DC,
120-127 VAC/DC, 220-240 VAC/DC, 240-250 VAC/DC, 380-400 VAC, 415-440 VAC, 480-500
VAC; 50/60Hz

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证


证书编号：CQC2014010307677590


本证书及附件应同时使用，信息查验说明见证书页

纸号：147817

型号解释：

Emax 2 系列万能式断路器





中国质量认证中心