产品认证证书

II型自愿认证

证书编号：CQC2018010304059156

发证日期：2022年03月22日

有效期至：2032年03月21日

委托人名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
生产企业名称及生产地址	ABB Bulgaria EOOD – Rakovski branch District Plovdiv, municipality Stryama, village Stryama 4142, Industrial Zone Rakovski, industrial road 1, nr. 14-18.
产品名称和系列、规格、型号	接触器 A9，A12，A16;详见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年08月21日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 签发

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0151691

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2018010304059156

Valid from: Mar.22,2022

Valid until: Mar.21,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND LOCATION OF THE FACTORY	ABB Bulgaria EOOD – Rakovski branch District Plovdiv, municipality Stryama, village Stryama 4142, Industrial Zone Rakovski, industrial road 1, nr. 14-18.
PRODUCT NAME, MODEL AND SPECIFICATION	Contactor A9 , A12 , A16;see the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.21,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 陈昕

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE

中国质量认证中心

C(2) 0151691

产品认证证书

II型自愿认证

证书编号：CQC2018010304059156

本证书及附件应同时使用，信息查验说明见证书页

纸号：151691

A9，A12，A16
Uimp:8kV;
Ui: 1000V;
Ith: A9:26A, A12:28A, A16:30A;
A9: AC-1: Ue/Ie: 690V/25A;
AC-3:Ue/Ie:220-230-240-380-400-415-440-500V/9A,690V/7A;
AC-8a: Ue/Ie: 400V/12A;
A12: AC-1: Ue/Ie: 690V/27A;
AC-3:Ue/Ie:220-230-240-380-400-415-440-500V/12A,690V/9A;
AC-8a: Ue/Ie: 400V/16A;
A16: AC-1: Ue/Ie: 690V/30A;
AC-3:Ue/Ie:220-230-240-380-400-415V/17A,440V/16A,500V/14A,690V/10A;
AC-8a: Ue/Ie: 400V/22A;
Us: 24V 50/60Hz, 48V 50/60Hz,110V 50Hz/110-120V 60Hz,
220-230V 50Hz/230-240V 60Hz,380-400V 50Hz/400-415V 60Hz,
400-415V 50Hz/415-440V 60Hz;
IP20;
极数: 3P,4P;
配用的辅助触头：(本体)
Ith: 16A;
AC-15:Ue/Ie:24-127V/6A,220-240V/4A,380-440V/3A,500-690V/2A;
DC-13:Ue/Ie:24V/6A,48V/2.8A,72V/2A,110-125V/1.1A,220-250V/0.55A
1 NO , 1NC ,1NO1NC, 2NO2NC, 3NO2NC,

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书
II型自愿认证

证书编号：CQC2018010304059156

本证书及附件应同时使用，信息查验说明见证书页

纸号：151691

型号解释:

IV - Auxiliary Pole Construction 常开辅助触点对数和常闭辅助触点对数

00 – No auxiliary pole provided.

01 – 1 normally closed auxiliary pole.

10 – 1 Normally opened auxiliary pole.

22 – 2 Normally Opened and 2 Normally Closed auxiliary poles.

32 – 3 Normally Opened and 2 Normally Closed auxiliary poles.

V - Coil code 线圈代号

Control voltage		Coil code
50Hz	60Hz	
24	24	81
48	48	83
110	110-120	84
220-230	230-240	80
380-400	400-415	85
400-415	415-440	86

List of type

Designation
A9-30-10 + coil voltage
A9-30-01 + coil voltage
A9-30-22 + coil voltage
A9-30-32 + coil voltage
A9-40-00 + coil voltage
A9-22-00 + coil voltage
A12-30-10 + coil voltage

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2018010304059156

本证书及附件应同时使用，信息查验说明见证书页

纸号：151691

A12-30-01 + coil voltage
A12-30-22 + coil voltage
A12-30-32 + coil voltage
A16-30-10 + coil voltage
A16-30-01 + coil voltage
A16-30-22 + coil voltage
A16-30-32 + coil voltage
A16-40-00 + coil voltage
A16-22-00 + coil voltage

中国质量认证中心