产品认证证书

II型自愿认证

证书编号：CQC2018010307085408

发证日期：2022年02月15日
有效期至：2032年02月15日

委托人名称及注册地址	ABB S.P.A. Via C. Pescaria n°5, 24123 Bergamo - ITALY
制造商名称及注册地址	ABB S.P.A. Via C. Pescaria n°5, 24123 Bergamo - ITALY
生产企业名称及生产地址	ABB S.P.A. Via Enrico Fermi n°40, 03100 Frosinone Italy
产品名称和系列、规格、型号	塑料外壳式断路器 T4N/PV-E;具体参数和型号解释详见附件
产品标准和技术要求	GB/T 14048.2-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年09月02日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 签发

中国质量认证中心

C(2) 0138154

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2018010307085408

Valid from: Feb.15,2022

Valid until: Feb.15,2032

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB S.P.A. Via C. Pescaria n°5, 24123 Bergamo - ITALY
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB S.P.A. Via C. Pescaria n°5, 24123 Bergamo - ITALY
NAME AND LOCATION OF THE FACTORY	ABB S.P.A. Via Enrico Fermi n°40, 03100 Frosinone Italy
PRODUCT NAME, MODEL AND SPECIFICATION	Moulded Case Circuit-breaker T4N/PV-E;See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.2-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Sep.02,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 陈昕

SIGNATURE 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0138154

产品认证证书


II型自愿认证

证书编号：CQC2018010307085408

本证书及附件应同时使用，信息查验说明见证书页

纸号：138154

T4N/PV-E
Ui: 1500V;
Uimp: 8kV;
Ue:DC1500V;
In: 32A,40A, 50A, 80A, 100A, 125A, 150A, 160A, 175A, 200A, 225A, 250A;
额定运行短路分断能力 Ics(kA): 7.5kA;
额定极限短路分断能力 Icu(kA): 10kA;
选择性类别: A;
过电流脱扣器类型: 热磁式;
适用于隔离;
直流接线图如下：



Type B and D 不适用于 250A

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证

证书编号：CQC2018010307085408

本证书及附件应同时使用，信息查验说明见证书页

纸号：138154

型号解释：

T4 N /PV -E 250



250 = Max Rated Current
最大额定电流

-E = 1500Vdc
1500V

/PV = Photovoltaic Application
光伏应用

Breaking Level 分断等级

N = Normal
一般

T4 = 250A Frame Size
250A框架等级

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心