产品认证证书

II型自愿认证

证书编号：CQC20012273065

发证日期：2021年10月20日
有效期至：2031年10月20日

委托人名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
制造商名称及注册地址	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
生产企业名称及生产地址	ABB新会低压开关有限公司 广东省江门市新会区今古洲工业开发区
产品名称和系列、规格、型号	接触器 AF80-30-**-**, AF80-40-**-**, AF80-22-**-**, AF96-30-**-**; 规格参数详见附件
产品标准和技术要求	GB/T 14048.4-2020
认证模式	产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC12-000001-2020认证规则的要求，特发此证。

本证书为变更证书，证书首次颁发日期：2020年11月08日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站（www.cnca.gov.cn）查验证书信息

授权签字人 刘江　　签发 谢肇煦

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

C(2) 0109563

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC20012273065

Valid from: Oct.20,2021

Valid until: Oct.20,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND REGISTERED ADDRESS OF THE MANUFACTURER	ABB France 11 Rue d' Arsonval 69680, Chassieu, FRANCE
NAME AND LOCATION OF THE FACTORY	ABB Xinhui Low Voltage Switchgear Co.,Ltd. Jinguzhou Industrial Development Zone Xinhui Region,Jiangmen City, Guangdong Province, P.R.China
PRODUCT NAME, MODEL AND SPECIFICATION	Contactor AF80-30-**-**, AF80-40-**-**, AF80-22-**-**, AF96-30-**-**; See the Appendix
THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS	GB/T 14048.4-2020
TYPE OF CERTIFICATION SCHEMES	Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Nov.08,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn

SIGN BY 刘江 **SIGNATURE** 谢肇煦

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China Tel: +86 10 83886666

C(2) 0109563

产品认证证书

II型自愿认证

证书编号 CQC20012273065

本证书及附件应同时使用，信息查验说明见证书页

纸号：109563

上报参数：

AF80-30-**-**, AF80-40-**-**, AF80-22-**-**, AF96-30-**-**

Uimp: 8kV;

Ui:1000V;

AF80-30-**-**：Ith:130A;

AC-1:Ue/Ie:1000V/50A,690V/125A;

AC-3:Ue/Ie:220-440V/80A,500V/65A,690V/49A,1000V/25A;

AC-4:Ue/Ie:220-500V/65A,690V/40A;

AC-8a:Ue/Ie:400V/105A;

AC-3e:Ue/Ie:220-440V/80A,500V/65A,690V/49A;

AF80-40-**-**：Ith:125A;

AC-1:Ue/Ie:1000V/50A,690V/125A;

AC-3:Ue/Ie:220-440V/80A,500V/65A,690V/49A,1000V/25A;

AC-4:Ue/Ie:220-500V/65A,690V/40A;

AF80-22-**-**：Ith:125A;

AC-1:Ue/Ie:1000V/50A,690V/125A;

AC-3:Ue/Ie:220-440V/80A,500V/65A,690V/49A,1000V/25A;

AC-4:Ue/Ie:220-500V/65A,690V/40A;

AF96-30-**-**：Ith:130A;

AC-1:Ue/Ie:1000V/60A,690V/130A;

AC-3:Ue/Ie:220-440V/96A,500V/80A,690V/57A,1000V/30A;

AC-4:Ue/Ie:220-500V/76A,690V/45A;

AC-8a:Ue/Ie:400V/120A;

AC-3e:Ue/Ie:220-440V/96A,500V/80A,690V/57A;

Us: 24-60V 50/60Hz, 24-60V 50/60Hz/20-60V DC,

48-130V 50/60Hz/DC,100-250V 50/60Hz/DC, 250-500V 50/60Hz/DC;

3P,4P;

IP10;

配用的辅助触头：

1NO,1NC,2NO2NC;

Ith:16A;

CA4-***, CAT4-***, VE4: CQC2013010304651497

中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

产品认证证书

II型自愿认证

证书编号 CQC20012273065

本证书及附件应同时使用，信息查验说明见证书页 纸号：109563

AC-15:Ue/Ie:24-127V/6A,220-240V/4A,380-440V/3A,500-690V/2A;
DC-13:Ue/Ie:24V/6A,48V/4A,72V/1A,110-125V/0.55A,
220-250V/0.27A,400V/0.15A,500V/0.13A,600V/0.1A;
CAL4-**, CA4-**, CC4-**: CQC2011010304496319, CQC2020980304001053
AC-15:Ue/Ie:127V/6A,240V/4A,400V/3A,440V/3A,500V/2A,690V/2A;
DC-13:Ue/Ie:24V/6A,48V/4A,72V/1A,125V/0.55A,
250V/0.27A,400V/0.15A,500V/0.13A,600V/0.1A

型号解释：

AF	80	- 30 -	00 -	11
I	II	III	IV	V

I –基本系列 Main designation: AF

II - 400V, AC-3 应用类别下额定工作电流 Range size

80, 96

III– 主触点的状态 Main Pole Construction

22 – 2 个常开触点和 2 个常闭触点.

22 – 2 Normally Opened and 2 Normally Closed main poles.

30 – 3 个常开触点和 0 个常闭触点.

30 – 3 Normally Opened and 0 Normally Closed main poles.

40 – 4 个常开触点和 0 个常闭触点.

40 – 4 Normally Opened and 0 Normally Closed main poles.

IV– 辅助触点的状态 Auxiliary Pole Construction

00–无辅助触点

00– No auxiliary pole provided.

11–1 个常开辅助触点和 1 个常闭辅助触点

11 – One Normally Opened and one Normally Closed auxiliary poles.

22 –2 个常开辅助触点和 2 个常闭辅助触点

（AF80-40-**与 AF80-22-**型号的接触器没有此种辅助触点形式）

22 – Two Normally Opened and two Normally Closed auxiliary poles.

中国质量认证中心

产品认证证书

II型自愿认证

证书编号 CQC20012273065

本证书及附件应同时使用，信息查验说明见证书页 纸号：109563

V– 线圈代码 Coil code

11 : 24-60V 50/60Hz 20-60V DC

41 : 24-60V 50/60Hz

12 : 48-130V 50/60Hz-DC

13 : 100-250V 50/60Hz-DC

14 : 250-500V 50/60Hz-DC

中国质量认证中心