

Stanilite®

Platinum exit LED jumbo Nexus®



Range

Platinum range

Product group

Exit LED



Features

- High emergency classification
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Microprocessor controlled integrated AC/emergency LED driver
- Architecturally pleasing and lightweight design
- Available in all pictograph diffuser options
- Wall mount or ceiling mount versions available to cover all installation requirements
- Exit can also be suspended via jack chain, rod and lanyard (not supplied) if required
- Large terminal block (16mm²) for easy wiring
- Viewing distance 40m
- Protective wire guard available - ceiling/suspended mount and wall mount

Catalogue no.	Description
---------------	-------------

Nexus products

PEJLLXCM-1	Platinum exit LED jumbo Nexus LX ceiling mount single sided picto
PEJLLXCM-2	Platinum exit LED jumbo Nexus LX ceiling mount single sided <picto
PEJLLXCM-3	Platinum exit LED jumbo Nexus LX ceiling mount single sided picto>
PEJLLXCM-5	Platinum exit LED jumbo Nexus LX ceiling mount double sided picto
PEJLLXCM-6	Platinum exit LED jumbo Nexus LX ceiling mount double sided picto AOW
PEJLRFCM-1	Platinum exit LED jumbo Nexus RF ceiling mount single sided picto
PEJLRFCM-2	Platinum exit LED jumbo Nexus RF ceiling mount single sided <picto
PEJLRFCM-3	Platinum exit LED jumbo Nexus RF ceiling mount single sided picto>
PEJLRFCM-5	Platinum exit LED jumbo Nexus RF ceiling mount double sided picto
PEJLRFCM-6	Platinum exit LED jumbo Nexus RF ceiling mount double sided picto AOW

Accessories

PEJWMKIT	Bracket wall mounting economy jumbo exit white (kit contains 2 brackets)
26-CJMD007	Wire guard - wall mount

Spare parts

03-01307P	Battery LiFePO4 6.4V 3.2Ah
31-PEJ1	DIFF ECO JUMBO 18W SS PICTO
31-PEJ2	DIFF ECO JUMBO 18W SS <PICTO
31-PEJ3	DIFF ECO JUMBO 18W SS PICTO>
31-PEJ5	DIFF ECO JUMBO 18W DS PICTO
31-PEJ6	DIFF ECO JUMBO 18W DS PICTO AOW



Dimensions

Length	Width	Height
615mm	123mm	310mm

Weight

Model	Weight
Nexus LX/RF	4.5kg

Construction

Part	Construction
Body	White powder coated zinc steel
Diffuser	Opal acrylic

Light source			
	Model	Light source	
	Nexus LX/RF	Multiple LED 4W	

Power consumption			
	Model	Power consumption	
	Nexus LX/RF	9W average, 12W maximum	

Photometrics			
	Model	Class	Classification
	Nexus LX/RF	C0	D32
		C90	D10

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards