



Nordicab low voltage distribution cabinet

Made to make life easier. Built to last a lifetime.



- Easy installation
- Improved design
- Proven reliability

Nordicab low voltage distribution cabinets



Nordicab low voltage distribution cabinets by ABB are easy to install and built to last. Based on our proven platform, they include improvements and features requested by our customers which make life easier for installation engineers. They resist both impacts and the elements, and ensure durability and safe, reliable electrical distribution in all environments.

Based on
our proven platform



Available in
3 widths



Includes improvements
based on customer
requests



Safe and reliable
in all environments



Easy to install
and built to last



A complete, tested
and **verified solution**



Easy installation

The new Nordicab low voltage distribution cabinet with the Z-busbar system enables safer and more convenient installation. More space for cabling and connection and a new solution for the pull-out legs makes life easier for installers. It's a complete solution that's designed to work together as a system.



Improved design

The design incorporates numerous improvements that we developed in response to customer feedback. From the adjustable, pull-out legs to the lighter door and improved temporary outlet, the design has been modernized and improved both inside and out.



Proven reliability

Nordicab is built to provide many years of continuous, trouble-free operation. With verified IEC 61439-5 arctic climate impact resistance and IP34D ingress protection it is durable enough for the harshest weather conditions.

Available in
3 widths



NC350



NC600



NC850

Cable distribution cabinets

Type	ID number	Dimensions [mm]			Free busbar [mm]	Rated current [A]	Lock
		W	H	D			
Cable distribution cabinets with busbar system							
NC350-G-SE-Z4	2CGD000585A2112	350	1200	260	261	400	EBR 2-stift
NC350-G-SE-Z6	2CGD000585A3112	350	1200	260	261	630	EBR 2-stift
NC600-G-SE-Z4	2CGD000585A2212	600	1200	260	511	400	EBR 2-stift
NC600-G-SE-Z6	2CGD000585A3212	600	1200	260	511	630	EBR 2-stift
NC850-G-SE-Z6	2CGD000585A3312	850	1200	260	761	630	EBR 2-stift

Type	ID number	Dimensions [mm]			Mounting dim. [mm]			Lock
		W	H	D	W	H	D	
Enclosures with mounting plate								
NC350-G-SE-M	2CGD000585A1112	350	1200	260	300	700	230	EBR 2-stift
NC600-G-SE-M	2CGD000585A1212	600	1200	260	550	700	230	EBR 2-stift
NC850-G-SE-M	2CGD000585A1312	850	1200	260	800	700	230	EBR 2-stift



—
new.abb.com