

Pedestals

EH3 / GD - Accessories

EH3 - Accessories







Product	Type	Order code	Pack
Locks with profile half cylinder			
	With 2 keys , V2432-E		
	EH3AEECI	4TBE843001C0100	1
	Spare keys for EH3AEECI		
	PS832022	4TBP832022C0100	2
	With 1 square key, 8 mm		
	EH3AEEQH	4TBE843002C0100	1
	With an 8 mm triangular key		
	EH3AEETH	4TBE843003C0100	1
	With 2 keys A434		
	EH3UAECI	4TBE843248C0100	1
Spare keys upon request.			


Diagram holder

	DIN A4 - W x H = 325 x 180 mm		
	AC811516	4TBC811516C0100	1
	DIN A5 - W x H= 155 x 225 mm		
	PS832000	4TBP832000C0100	1

IP44 ventilation grille

	Set of 2 pieces		
	PS832019	4TBP832019C0100	1
	Suitable for a ventilation opening Includes 2 grilles and 4 nylon nails. Total insulation. RAL 7035		

Threaded insert

	M8 threaded insert		
	Dodge-type for rear wall and door.		
	APTIM4	4TBO851026C0100	100
	Punch for inserting M8 threaded barrel.		
	EHUOEEEG	4TBC844039C0100	1

Product	Type	Order code	Pack
---------	------	------------	------

Vandal proof nameplate holder


Can be placed on every flat surface, by drilling two holes Ø 5.5 mm; the identification window is used as a drill template. Steady against vandalism; it keeps its total isolation. Possibility to write on manually and/or to use the standard lettering systems; the maximal letter height is 18 mm. Usefull dimensions of letters: 18 x 143. Outside dimensions: 30 x 183 x 5.

	EH3AEEE4	4TBE843304C0100	1


Handle

	Handle for lock with a profile half cylinder		
	EH3EEESH	4TBE843000C0100	1
	Spare part		

Double closure handle

	For two locks with profile half cylinder		
	EH3AEEDH	4TBE783042C0100	1
	Spare part (Note: for after-market installation, an operation is required on the door mechanism).		

Concrete base (kit)

	Size: DIN00		
	EH3REXEJ	4TBE843272C0100	1
	Size: DIN0		
	EH3RE0EJ	4TBE843273C0100	1
	Size: DIN1		
	EH3RE1EJ	4TBE843274C0100	1
	Size: DIN2		
	EH3RE2EJ	4TBE843275C0100	1
	Size: DIN3		
	EH3RE3EJ	4TBE843276C0100	1