

SACE Emax 2 - Formula AIR - Megamax HF2

Piastre di sollevamento - E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2



Lifting plates - E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2

Hebeplatten - E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2


Plaques de levage - E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2

Placas de elevación - E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2


E2.2-E4.2-E6.2-FA2-FA4-HF2.2-HF4.2




1



2





Per sollevare l'interruttore usare solo le piastre originali ABB, contenute in questo kit.

Use only original ABB plates, contained in this kit, to raise the circuit breaker.

Verwenden Sie zum Anheben des Leistungsschalters nur die in diesem Satz enthaltenen ABB-Originalplatten.

Utiliser uniquement les plaques d'origine ABB, contenues dans ce kit, pour soulever l'interrupteur.

Utilice sólo las placas originales de ABB, contenidas en este kit, para levantar el interruptor.

	Fisso Fixed Fest Fixe Fijo			Parte mobile di estraibile Moving part of withdrawable device Bewegliches Teil ausfahrbare Ausführung Partie mobile de débrochable Parte móvil de extraíble		
	III	IV	Fs	III	IV	Fs
E2.2-FA2-HF2.2	41 Kg / 90 lbs	53 Kg / 117 lbs		48 Kg / 106 lbs	55 Kg / 121 lbs	
E4.2-FA4-HF4.2	56 Kg / 123 lbs	70 Kg / 154 lbs		60 Kg / 132 lbs	74 Kg / 163 lbs	
E6.2	109 Kg / 240 lbs	125 Kg / 276 lbs	140 Kg / 309 lbs	120 Kg / 265 lbs	134 Kg / 295 lbs	148 Kg / 326 lbs
E2.2-A	45 Kg / 99 lbs	58 Kg / 128 lbs		54 Kg / 119 lbs	63 Kg / 139 lbs	
E4.2-A	59 Kg / 130 lbs	74 Kg / 163 lbs		68 Kg / 150 lbs	84 Kg / 185 lbs	
E6.2-A	115 Kg / 254 lbs	132 Kg / 291 lbs	148 Kg / 326 lbs	136 Kg / 300 lbs	152 Kg / 335 lbs	169 Kg / 373 lbs