




CIRCUIT BREAKER LUGS: CATALOG DATA				
CIRCUIT BREAKER CAT NO. PREFIX	AMPERE RATING	BREAKER LUG CATALOG NUMBER		WIRE SIZE (AWG/KCMIL)
XT5	250-600A	KXT5CUAL350K-3PC	KXT5CUAL350K-4PC	(1) #6-350 CU-AL
		KXT5CUAL500K-3PC	KXT5CUAL500K-4PC	(1) 250-500 CU-AL
		KXT5CUAL2X500K-3PC	KXT5CUAL2X500K-4PC	(2) #2/0-500 CU-AL
		KXT5CUAL1X750KC-3	KXT5CUAL1X750KC-4	(1) 350-600 CU-AL

FIELD INSTALLABLE NEUTRAL ASSEMBLY AND GROUND KIT			
CAT NO. PREFIX	TYPE	AMPERE RATING	WIRE SIZE (AWG/KCMIL)
TGL6	GROUND KIT	600-1200A	(3) #2-250 CU-AL
TNIA400 TNIA400XTGF	NEUTRAL ASM	125-400A	(1) #4-600 CU-AL (2) #1/0-250 CU-AL
TNIA600 TNIA600XTGF	NEUTRAL ASM	225-600A	(2) #2/0-500 CU-AL

KNOCKOUTS				
SYMBOLS	CONDUIT SIZE		DIAMETER	
	IN	MM	IN	MM
A	3 1/2	89	4 1/8	105
B	3	76	3 3/5	91

- NOTES:
1. MATERIAL: LOW CARBON STEEL
 2. FINISH: ELECTROCOAT ENAMEL, GRAY
 3. AGENCY APPROVAL: cULus LISTED -FILE E11592
 4. SUITABLE FOR USE AS SERVICE EQUIPMENT WHEN NEUTRAL ASSEMBLY IS INSTALLED
 5. THE SHORT CIRCUIT RATING OF THIS ENCLOSED CIRCUIT BREAKER IS EQUAL TO THE INTERRUPTING RATING, AT THE SUPPLY VOLTAGE MARKED ON THE CIRCUIT BREAKER INSTALLED
 6. FOR ALTERNATE LUGS CONSULT THE BUYLOG

THIRD ANGLE		SHEET#	DWG NO.	DATE	REV
		1 of 1	208C2838SH3	20-Jan-22	4

ABB		
OUTLINE-NEMA 3R XT5ENCL600R		
DWG NO.	DATE	REV
208C2838SH3	20-Jan-22	4