



OHB OUTDOOR CB SPARE LIST



Sr	Article no.	Description	Photo
1	1VYN300250-105	AUX. SWITCH (TYPE-35V9275) 13NO+13NC	
2	1VYN401001-EF1	MAGNET ASSEMBLY (FOR INDIAN MKT.). VDC	
3	IN54450007-AB	Close/tripCoil 24V DC	
4	IN54450007-Y	Close/tripCoil 30V DC	
5	IN54450007-K	Close/tripCoil 110V DC	




Sr	Article no.	Description	Photo
6	IN54450007-G	Close/tripCoil 220V DC	
7	508003-803	Motor 110V DC	
8	508003-804	Motor 220V AC/DC	
9	1VYN301250-015	GAS FILLING DVEICE FOR OHB / VBF & SDB	
10	1VYN401201-BC	DAMPER ASSY.(161025801) FOR OHB	

Sr	Article no.	Description	Photo
11	1VYN401201-CB	TRIPPING SPRING ASSY. FOR : OHB	
12	1VYN401201-EZ	pole assly without vent valve (8pt)	
13	1VYN401250-073	Top Cap for OHB	
14	507893-803	BASIC MECHANISM (ESH9) HD4 & OHB	
15	508574-801-EX	Variant for 508574-801 export with 9pt	

Sr	Article no.	Description	Photo
16	SWT-431336-P11	SF6 GAS CYLINDER(3.75Kg)	
17	1VCR002985G0001	MO2 Assy. (24Vcc)(Additional Trip)	
18	1VCR002985G0003	MO2 Assy. (48Vca-Vcc)(Additional Trip)	
19	1VCR002985G0005	MO2 Assy.(110-127Vca/110-132Vcc)ADD. TR.	
20	1VCR002985G0007	MO2 Assy. (220-250Vca/220-250Vcc)ADD. TR	

Sr	Article no.	Description	Photo
21	1VCR004289G0001	Opening coil 24VDC MO	
22	1VCR004289G0003	VD4 MO Opening coil 48VDC	
23	1VCR004289G0005	Open. Coil Mo1 (110-132V DC)	
24	1VCR004289G0007	Open. Coil Mo1 (220-250V DC/220-250V AC)	
25	1VCR004290G0001	MU Coil Assly. (24V DC) (Undervoltage)	

Sr	Article no.	Description	Photo
26	1VCR004290G0003	MU. Coil Assly.(48V AC-DC)(Undervoltage)	
27	1VCR004291G0001	SHUNT CLOSING RELEASE - MC 24VDC	
28	1VCR004291G0003	VD4 MC Closing Coil (48V AC-DC))	
29	1VCR004291G0005	MC Closing Coil(110-132V DC)	
30	1VCR004291G0007	MC Closing Coil(220-250V DC/220-250V AC)	

Sr	Article no.	Description	Photo
31	507412-801	Operation Box Assembly	
32	507893-803	BASIC MECHANISM (ESH9) HD4 & OHB	
33	1VCR002352G0001	Coil SUPPORT (EL) (1VCF339799R0271)	
34	NZN000859P11	SWITCH ELEMENT S826 E/L	