

Indoor Capacitor Fuses

Voltage (kV)	Current Rating (A)	Bus Mount		Bushing Mount	
		Cooper X-Limiter	Hi-Tech EX	Cooper X-Limiter	Hi-Tech EX
4.3	18	43F018-IVBT	HTEX22T018	43F018-IVBTB	HTEX22D018
	25	43F025-IVBT	HTEX22T025	43F025-IVBTB	HTEX22D025
	35	43F035-IVBT	HTEX22T030	43F035-IVBTB	HTEX22D030
	45	43F045-IVBT	HTEX22T040	43F045-IVBTB	HTEX22D040
	50	43F050-IVBT	HTEX22T050	43F050-IVBTB	HTEX22D050
	65	43F065-IVBT	HTEX22T065	43F065-IVBTB	HTEX22D065
	75	43F075-IVBT	HTEX22T075	43F075-IVBTB	HTEX22D075
	100	43F100-IVBT	HTEX32T100	43F100-IVBTB	HTEX32D100
	130	-	-	43F130-IVBTU **	HTEX32D125
	150	-	-	43F150-IVBTU **	HTEX32D150
5.5	200	-	-	43F200-IVBTU **	HTEX32D200
	18	55F018-IVBT	HTEX22T018	55F018-IVBTB	HTEX22D018
	20	55F020-IVBT	HTEX22T020	55F020-IVBTB	HTEX22D020
	25	55F025-IVBT	HTEX22T025	55F025-IVBTB	HTEX22D025
	30	55F030-IVBT	HTEX22T030	55F030-IVBTB	HTEX22D030
	40	55F040-IVBT	HTEX22T040	55F040-IVBTB	HTEX22D040
	50	55F050-IVBT	HTEX22T050	55F050-IVBTB	HTEX22D050
	65	55F065-IVBT	HTEX22T065	55F065-IVBTB	HTEX22D065
	75	55F075-IVBT	HTEX22T075	55F075-IVBTB	HTEX22D075
	100	-	-	55F100-IVBTU **	HTEX32D100
8.3	130	-	-	55F130-IVBTU **	HTEX32D125
	150	-	-	55F150-IVBTU **	HTEX32D150
	10	83F010-IVBT	HTEX23T010	83F010-IVBTB	HTEX23D010
	12	83F012-IVBT	HTEX23T012	83F012-IVBTB	HTEX23D012
	18	83F018-IVBT	HTEX23T018	83F018-IVBTB	HTEX23D018
	20	83F020-IVBT	HTEX23T020	83F020-IVBTB	HTEX23D020
	25	83F025-IVBT	HTEX23T025	83F025-IVBTB	HTEX23D025
	30	83F030-IVBT	HTEX23T030	83F030-IVBTB	HTEX23D030
	40	83F040-IVBT	HTEX23T040	83F040-IVBTB	HTEX23D040
	50	83F050-IVBT	HTEX23T050	83F050-IVBTB	HTEX23D050
15.5	65	83F065-IVBT	HTEX33T065	83F065-IVBTB	HTEX33D065
	80	83F080-IVBT	HTEX33T080	83F080-IVBTB	HTEX33D080
	100	83F100-IVBT	HTEX33T100	83F100-IVBTB	HTEX33D100
	125	83F125-IVBT	HTEX33T125	83F125-IVBTB	HTEX33D125
	6	155F006-IVBT	HTEX24T006	155F006-IVBTB	HTEX24D006
	8	155F008-IVBT	HTEX24T008	155F008-IVBTB	HTEX24D008
	10	155F010-IVBT	HTEX24T010	155F010-IVBTB	HTEX24D010
	12	155F012-IVBT	HTEX24T012	155F012-IVBTB	HTEX24D012
	18	155F018-IVBT	HTEX24T018	155F018-IVBTB	HTEX24D018
	20	155F020-IVBT	HTEX24T020	155F020-IVBTB	HTEX24D020
23	25	155F025-IVBT	HTEX24T025	155F025-IVBTB	HTEX24D025
	30	155F030-IVBT	HTEX24T030	155F030-IVBTB	HTEX24D030
	40	155F040-IVBT	HTEX24T040	155F040-IVBTB	HTEX24D040
	50	155F050-IVBT	HTEX24T050	155F050-IVBTB	HTEX24D050
	65	155F065-IVBT	HTEX34T065	155F065-IVBTB	HTEX34D065
	80	155F080-IVBT	HTEX34T080	155F080-IVBTB	HTEX34D080
	100	155F100-IVBT	HTEX34T100	155F100-IVBTB	HTEX34D100
	6	23F006-IVBT	HTEX25T006	23F006-IVBTB	HTEX25D006
	8	23F008-IVBT	HTEX25T008	23F008-IVBTB	HTEX25D008
	10	23F010-IVBT	HTEX25T010	23F010-IVBTB	HTEX25D010
23	12	23F012-IVBT	HTEX25T012	23F012-IVBTB	HTEX25D012
	18	23F018-IVBT	HTEX25T018	23F018-IVBTB	HTEX25D018
	20	23F020-IVBT	HTEX25T020	23F020-IVBTB	HTEX25D020
	25	23F025-IVBT	HTEX25T025	23F025-IVBTB	HTEX25D025
	30	23F030-IVBT	HTEX25T030	23F030-IVBTB	HTEX25D030
	40	23F040-IVBT	HTEX25T040	23F040-IVBTB	HTEX25D040
	50	23F050-IVBT	HTEX25T050	23F050-IVBTB	HTEX25D050

Note: ** Indicates parallel fuses.

Outdoor Capacitor Fuses

Voltage (kV)	Current Rating (A)	Bus Mount		Bushing Mount	
		Cooper X-Limiter	Hi-Tech EX	Cooper X-Limiter	Hi-Tech EX
4.3	18	43F018-OVBT	HTEX22U018	43F018-OVBTB	HTEX22C018
	25	43F025-OVBT	HTEX22U025	43F025-OVBTB	HTEX22C025
	35	43F035-OVBT	HTEX22U030	43F035-OVBTB	HTEX22C030
	45	43F045-OVBT	HTEX22U040	43F045-OVBTB	HTEX22C040
	50	43F050-OVBT	HTEX22U050	43F050-OVBTB	HTEX22C050
	65	43F065-OVBT	HTEX22U065	43F065-OVBTB	HTEX22C065
	75	43F075-OVBT	HTEX22U075	43F075-OVBTB	HTEX22C075
	100	43F100-OVBT	HTEX32U100	43F100-OVBTB	HTEX32C100
	130	-	-	43F130-OVBTU **	HTEX32C125
	150	-	-	43F150-OVBTU **	HTEX32C150
5.5	200	-	-	43F200-OVBTU **	HTEX32C200
	18	55F018-OVBT	HTEX22U018	55F018-OVBTB	HTEX22C018
	20	55F020-OVBT	HTEX22U020	55F020-OVBTB	HTEX22C020
	25	55F025-OVBT	HTEX22U025	55F025-OVBTB	HTEX22C025
	30	55F030-OVBT	HTEX22U030	55F030-OVBTB	HTEX22C030
	40	55F040-OVBT	HTEX22U040	55F040-OVBTB	HTEX22C040
	50	55F050-OVBT	HTEX22U050	55F050-OVBTB	HTEX22C050
	65	55F065-OVBT	HTEX22U065	55F065-OVBTB	HTEX22C065
	75	55F075-OVBT	HTEX22U075	55F075-OVBTB	HTEX22C075
	100	-	-	55F100-OVBTU **	HTEX32C100
8.3	130	-	-	55F130-OVBTU **	HTEX32C125
	150	-	-	55F150-OVBTU **	HTEX32C150
	10	83F010-OVBT	HTEX23U010	83F010-OVBTB	HTEX23C010
	12	83F012-OVBT	HTEX23U012	83F012-OVBTB	HTEX23C012
	18	83F018-OVBT	HTEX23U018	83F018-OVBTB	HTEX23C018
	20	83F020-OVBT	HTEX23U020	83F020-OVBTB	HTEX23C020
	25	83F025-OVBT	HTEX23U025	83F025-OVBTB	HTEX23C025
	30	83F030-OVBT	HTEX23U030	83F030-OVBTB	HTEX23C030
	40	83F040-OVBT	HTEX23U040	83F040-OVBTB	HTEX23C040
	50	83F050-OVBT	HTEX23U050	83F050-OVBTB	HTEX23C050
15.5	65	83F065-OVBT	HTEX33U065	83F065-OVBTB	HTEX33C065
	80	83F080-OVBT	HTEX33U080	83F080-OVBTB	HTEX33C080
	100	83F100-OVBT	HTEX33U100	83F100-OVBTB	HTEX33C100
	125	83F125-OVBT	HTEX33U125	83F125-OVBTB	HTEX33C125
	6	155F006-OVBT	HTEX24U006	155F006-OVBTB	HTEX24C006
	8	155F008-OVBT	HTEX24U008	155F008-OVBTB	HTEX24C008
	10	155F010-OVBT	HTEX24U010	155F010-OVBTB	HTEX24C010
	12	155F012-OVBT	HTEX24U012	155F012-OVBTB	HTEX24C012
	18	155F018-OVBT	HTEX24U018	155F018-OVBTB	HTEX24C018
	20	155F020-OVBT	HTEX24U020	155F020-OVBTB	HTEX24C020
23	25	155F025-OVBT	HTEX24U025	155F025-OVBTB	HTEX24C025
	30	155F030-OVBT	HTEX24U030	155F030-OVBTB	HTEX24C030
	40	155F040-OVBT	HTEX24U040	155F040-OVBTB	HTEX24C040
	50	155F050-OVBT	HTEX24U050	155F050-OVBTB	HTEX24C050
	65	155F065-OVBT	HTEX34U065	155F065-OVBTB	HTEX34C065
	80	155F080-OVBT	HTEX34U080	155F080-OVBTB	HTEX34C080
	100	155F100-OVBT	HTEX34U100	155F100-OVBTB	HTEX34C100
	6	23F006-OVBT	HTEX25U006	23F006-OVBTB	HTEX25C006
	8	23F008-OVBT	HTEX25U008	23F008-OVBTB	HTEX25C008
	10	23F010-OVBT	HTEX25U010	23F010-OVBTB	HTEX25C010
23	12	23F012-OVBT	HTEX25U012	23F012-OVBTB	HTEX25C012
	18	23F018-OVBT	HTEX25U018	23F018-OVBTB	HTEX25C018
	20	23F020-OVBT	HTEX25U020	23F020-OVBTB	HTEX25C020
	25	23F025-OVBT	HTEX25U025	23F025-OVBTB	HTEX25C025
	30	23F030-OVBT	HTEX25U030	23F030-OVBTB	HTEX25C030
	40	23F040-OVBT	HTEX25U040	23F040-OVBTB	HTEX25C040
	50	23F050-OVBT	HTEX25U050	23F050-OVBTB	HTEX25C050

Note: ** Indicates parallel fuses.