


TECHNICAL DATA SHEET

PMA Accessories - SVN4-P - Flat Gasket

For PG thread

PMA**Features & Benefits:**

- Suitable for sealing of PMA fittings with polyamide or metal threads

Ingress protection:

- IP68 (EN/IEC 60529) at fitting threads

Materials:

- NBR reinforced with aramide fibres (asbestos-free)

Compatible with:

- PMAFIX Pro, PMAFIX, PMA EMC System fittings

Chemical properties:

- Please refer to www.pma.ch (Technical Information / Chemical Resistance)


Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:

Part no.	Thread size	Dimensions in mm (nom.)			Weight	Packing unit
	PG	d1	d2	A	kg/100 pcs	pcs/PU
SVN4-07	7	12.5	16.5	2.0	0.02	50
SVN4-09	9	15.2	20.0	2.4	0.03	50
SVN4-11	11	18.6	24.0	2.7	0.05	50
SVN4-13	13.5	20.4	31.0	5.3	0.11	50
SVN4-16	16	22.5	31.0	4.3	0.12	50
SVN4-21	21	28.3	37.0	4.4	0.13	30
SVN4-29	29	37.0	48.0	5.5	0.20	20
SVN4-36	36	47.0	57.0	5.0	0.22	20
SVN4-42	42	54.0	65.0	5.5	0.28	10
SVN4-48	48	59.3	69.0	4.9	0.31	10

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	-50 ... +250°C		PMA DO 9.21-4510
Short-term	+350°C	(168 h)	PMA DO 9.21-4360

ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

