

TECHNICAL DATA SHEET

PMA Accessories - OVN2 - Conduit clip

Standard conduit clip

PMA**Features & Benefits:**

- Provides reliable fixation of PMA conduits within PMA IP68 fittings
- Easy installation
- Provides connection with a high degree of safety between conduit and fitting
- Can be easily re-opened with a screwdriver
- Fits both conduit profiles - fine (T) and coarse (G)

Materials:

- High-grade, specially formulated polyamide

Compatible with:

- PMAFIX fitting series

Self-extinguishing**Colour:**

- Dark grey

Chemical properties:

- Please refer to www.pma.ch
(Technical Information / Chemical Resistance)


Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:

Part no.	Conduit size	Dimensions in mm (nom.)				Weight	Packing unit
		A	B	C	F		
dark grey	NW					kg/100 pcs	pcs/PU
OVN2-07	7	12.5	14.0	14.0	6.0	0.0	100
OVN2-10	10	16.0	17.5	17.0	7.0	0.1	50
OVN2-12	12	19.0	21.0	19.0	6.0	0.1	50
OVN2-17	17	25.0	26.5	22.5	7.0	0.1	50
OVN2-23	23	32.0	34.0	27.5	10.5	0.2	30
OVN2-29	29	38.5	40.5	32.0	10.5	0.3	20
OVN2-36	36	42.0	49.5	39.0	8.5	0.3	40
OVN2-48	48	59.5	62.0	47.0	8.5	0.4	20

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	-50 ... +105°C		PMA DO 9.21-4510
Upper application temperature	+120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+160°C	(168 h)	PMA DO 9.21-4360

ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

