
MICROLECTRIC®



Service Entrance Masts and Accessories

Ref. No.	Steel	PVC	Description
1	**MM104**		100A - 1 1/4" Entrance cap for 2 1/2" mast
		E998G	100A - 1 1/4" Entrance cap
		E998H	100A - 1 1/2" Entrance cap
	MM105		150A/200A - 1 1/2" Entrance cap for 2 1/2" mast
	MM202		200A - 2" Entrance cap for 2 1/2". mast
	MM202P		200A - 2" Entrance cap for old style 2 3/4" mast
		E998J	200A - 2" Entrance cap
		E998K-UPC	200A - 2 1/2" Entrance cap
		E998L	320A - 3" Entrance cap
		E998N	320A/400A - 4" Entrance cap
	CIEFA-4		400A - 4" Entrance cap for 4" rigid conduit
2	**MM700**		Service mast ground clamp, wire range: 8–1/0 AWG
3	**MM380**		Guy attachment c/w oval eye
4	**M101**		100A - Light duty spool rack
	MM5101		100A - Light duty spool rack (Alberta only)
	MM201		200A - Heavy duty spool rack
	MM801		400A - Heavy duty spool rack, fits 3" and 4" rigid conduit
	SS401-E		Wall mount spool Rack
5	**W62-1**		Wedge clamp 2 – 6 ACSR
	W20-1		Wedge clamp 1/0 – 4 ACSR
6	**MM390**		Drop wire hook bracket
7	**MM300**		Service mast wire holder
8	**MM505N**		Roof flange with neoprene collar for 2 1/2" mast
	MM5505N		Roof flange with neoprene collar for 1 1/4" conduit
	MM506N		Neoprene roof flange for 2 1/2" mast
	MM507DN		Neoprene double roof flange for 2 1/2" masts
	MM806N		Neoprene roof flange, for 4" rigid conduit
9	**MM250**		1/2" "U" for 2 1/2" mast
10	**MM251**		Mast strap c/w two 3/8" x 4" lag screws
	MM252		Mast strap without lag screws
		E977GC	1 1/4" conduit strap
		E997HC	1 1/2" conduit strap
		E977JC-4-HD	2" conduit strap
		E977K	2 1/2" conduit strap
		E977L	3" conduit strap
		E977N	4" conduit strap
11	**MM400**		Mast clamp with 5/8" x 10" threaded bolt and 4" x 4" square washer
	MM401		2 1/2" mast clamp without hardware
	MM445		2 1/2" mast clamp with 5/8" x 4 1/2" threaded bolt and 4" x 4" washer
	MM5400		2 1/2" mast clamp with 1/2" x 10" threaded bolt and 4" x 4" washer
12	**MM600**		2 1/2" mast clamp with 5 1/2" spacer, 5/8" x 4 1/2" threaded bolt and 4" x 4" washer
	MM602		Masonry 5 1/2" spacer without hardware
	MM602LD		Masonry 5 1/2" light duty spacer without hardware
	MM603		Mast clamp and masonry 5 1/2" spacer without hardware
13	**MM8**		8 ft. x 2-1/2" O.D. mast
	MM9CM		9 ft. x 2-1/2" O.D. mast
	MM10		10 ft. x 2-1/2" O.D. mast
		49009CC	10ft x 1 1/4" Conduit
		49010CC	10ft x 1 1/2" Conduit
		49011CC	10 ft. x 2" Conduit
		49012CC	10 ft. x 2 1/2" Conduit
		49013CC	10 ft x 3" Conduit
		49015CC	10ft x 4" Conduit
	MM12		12 ft. x 2 1/2" O.D. mast
14	**MM140**		1 1/4" Female reducer
	MM140M		1 1/4" Male reducer
	MM150		1 1/2" Female reducer
	MM150M		1 1/2" Male reducer
	MM200M		2" Male Reducer
	MM200		2" Female reducer
	MM200P		2" Female reducer for old style 2-3/4" service masts
		E942J	2" Female adaptor
		E943G	1 1/4" Male terminal adaptor
		E943H	1 1/2" Male terminal adaptor
15	**MC250**		2-1/2" One-piece mast coupler
		E940J	2" Conduit coupler
		E940K	2 1/2" Conduit coupler
		E995G	1 1/4" Offset
16		**E991J**	2" Meter hub
	MH200		2 1/2" Mast hub with set screw
	MH12X		1 1/4" Rigid conduit threaded hub
		E991G	1 1/4" Conduit hub
	MH15X		1 1/2" Rigid conduit threaded mast hub
		E991H	1 1/2" Conduit hub
	MH20		2" Rigid conduit threaded hub
	MH30	**E991L**	3" Conduit hub
	MH40		4" Rigid conduit threaded hub
17	**MM605**		Meter socket mounting bracket
18	**MM604**		Masonry meter socket 4 7/8" spacer bracket

Complete product offering.