



PowerMark™ Plus Load Centres

Offer update

2022-10-01



PowerMark™ Plus Load Centers

Offer updates

PowerMark™ Plus Three-Phase Main Breaker 125-200A Type 1 and Type 3R Load Centers are re-designed to be delivered with SACE Formula A2 factory-installed main circuit breakers.

Load Centers affected:

Type 1: TMC30412C, TMC42412C

Type 3R: TMC42412R

Amperes (MB)	Catalogue Number Type 1 Indoor Enclosure	Catalogue Number Type 3R Outdoor Enclosure	Maximum Circuits			Total 1-Pole Spaces
			1" THQL			
			1P	2P	3P	
100	TMC12410C	–	12	6	4	12
100	TMC18410C	–	18	8	6	18
125	TMC30412C	–	30	14	10	30
200	TMC42420C	TMC42420R	42	20	14	42

3ph 120/208V Load Centre only accepts 1" THQL style breakers.

Offer updates

Load Centre Catalogue numbers remain the same, but modification number (MOD 2 or M02) will be added to the load center labels.

Example:

PowerMark Plus™ Load Centre

Panneau de Distribution

Main Breaker

Disjoncteur Principal

Ground bar included
Barre de mise à la terre incluse

125 AMPS AMPÈRES

30 Spaces Espaces

30 Circuits Circuits

TMC30412C	
Indoor Enclosure	
Boîtier pour l'intérieur	
Surface/Flush Mount	
Montage en surface / encastré	
Grey Front	
Façade grise	
208Y/120 VAC	3PH - 4W
MOD 2	K240@SAL240@
Country of Origin:	
Mexico	

7 83164 30623 1

PowerMark™ Plus Load Centres

Links to drawings

Main breaker, grey front, type 1 enclosure

Amperes	No. of 1" Spaces	Type 1 Enclosure, Surface/Flush, Cat. No.	Drawing #	Mod. No.	Front Cat. No.
100	12	TMC12410C	10103091SH156	M01	TMC124A
100	18	TMC18410C	10103091SH156	M01	TMC184A
125	30	TMC30412C	10103091SH293	M02	TMC304AA2
200	42	TMC42420C	10103091SH294	M02	TMC424AA2

Main lug, grey front, type 1 enclosure

Amperes	Number of 1" Spaces	Cat. No.	Drawing #	Mod. No.	Front Cat. No.
125	12	TLC12412C	10103091SH169	M01	TLC124A
150	18	TLC18415C	10103091SH178	M01	TLC184A
150	24	TLC24415C	10103091SH179	M01	TLC244A
200	30	TLC30420C	10103091-SH21	M01	TLC304A
200	42	TLC42420C	10103091SH176	M01	TLC424A
225	30	TLC30422C	10103091SH177	M01	TLC304B
225	42	TLC42422C	10103091SH177	M01	TLC424B



TMC30412C M02 without main breaker barrier and front

PowerMark™ Plus Load Centres

Links to drawings

Main breaker, grey cover, type 3R enclosure

Amperes	No. of 1" Spaces	Type 3R Enclosure, Surface/Flush, Cat. No.	Drawing#	Mod. No.
100	12	---		
100	18	---		
125	30	---		
200	42	TMC42420R	10103091SH283	M02

Main lug, grey cover , type 3R enclosure

Amperes	Number of 1" Spaces	Cat. No.	Drawing#	Mod. No.
125	12	TLC12412R	10103091SH171	M01
150	18	---	---	---
150	24	TLC24415R	10103091SH172	M01
200	30	TLC30420R	10103091SH174	M01
200	42	TLC42420R	10103091SH175	M01
225	30	---	---	---
225	42	---	---	---



TMC42412R

PowerMark™ Plus Load Centres

Technical support

Technical Support

- ep.support@ca.abb.com

ABB