

产品认证证书

II型自愿认证

证书编号: CQC2013010304646608

发证日期: 2021年10月18日

有效期至: 2031年10月18日

委托人名称 ABB France
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

制造商名称 ABB France
及注册地址 11 Rue d' Arsonval 69680, Chassieu, FRANCE

生产企业名称 ABB 新会低压开关有限公司
及生产地址 广东省江门市新会区今古洲工业开发区

产品名称和系列、规格、型号 接触器
AX06-30-□□-□□、AX09-30-□□-□□、AX12-30-□□-□□、AX18-30-□□-□□、
AX25-30-□□-□□; 规格参数详见附件

产品标准和技术要求 GB/T 14048.4-2020

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2020年08月14日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



授权签字人

刘江

签发

谢肇煦

中国质量认证中心



<http://www.cqc.com.cn>

中国·北京·南四环西路188号9区 100070

电话: +86 10 83886666

C(2) 0105849

CERTIFICATE OF PRODUCT CERTIFICATION

TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC2013010304646608

Valid from: Oct.18,2021

Valid until: Oct.18,2031

NAME AND REGISTERED ADDRESS OF THE APPLICANT ABB France
11 Rue d' Arsonval 69680, Chassieu, FRANCE

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER ABB France
11 Rue d' Arsonval 69680, Chassieu, FRANCE

NAME AND LOCATION OF THE FACTORY ABB Xinhui Low Voltage Switchgear Co.,Ltd.
Jinguzhou Industrial Development Zone, Xinhui District, Jiangmen City, Guangdong Province, P.R.China

PRODUCT NAME, MODEL AND SPECIFICATION contactor
AX06-30-□□-□□, AX09-30-□□-□□, AX12-30-□□-□□, AX18-30-□□-□□, AX25-30-□□-□□ ;See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 14048.4-2020

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.

Date of original issued: Aug.14,2020

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGN BY

刘江

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



产品认证证书

II型自愿认证

证书编号: CQC2013010304646608

第 1 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105849

型号: AX06-30-□□-□□、AX09-30-□□-□□、AX12-30-□□-□□、

AX18-30-□□-□□、AX25-30-□□-□□;

Uimp: 6kV;

Ui: 690V;

Ith: AX06: 22A, AX09: 24A, AX12: 26A, AX18: 28A, AX25: 32A;

使用类别、Ue、Ie:

使用类别	Ue(V~)	Ie(A)				
		AX06	AX09	AX12	AX18	AX25
AC-3	220-230-240V	7A	9A	12A	18A	25A
AC-3	380-400V	7A	9A	12A	18A	25A
AC-3	415V	7A	9A	12A	18A	25A
AC-3	440V	7A	9A	9A	12A	16A
AC-3	500V	6A	9A	9A	12A	14A
AC-3	690V	5A	7A	7A	9A	10A
AC-8a	400V	9A	12A	16A	22A	30A
AC-1	690V	20A	22A	25A	27A	32A

Us:

频率	Us (V~)									
50 Hz	24	48	105	110	190	200	220-230	230-240 0	380-40 0	400-415
60 Hz	24	48	110-1 27	110-1 20	220	200-22 0	230-240	240-26 0	400-41 5	415-440

极数: 3P;

防护等级: IP20 (仅适用于正面);



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2013010304646608

第 2 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105849

配用的辅助触头:

种类和对数: 1 对 X 型或 1 对 Y 型;

Ith: 16A;

使用类别、Ue、Ie:

使用类别	Ue (V)	Ie(A)
AC-15	24-127VAC	6
AC-15	220-240VAC	4
AC-15	380-440VAC	3
AC-15	500VAC	2
AC-15	690VAC	2
DC-13	24VDC	6
DC-13	48VDC	2.8
DC-13	72VDC	2
DC-13	125VDC	1.1
DC-13	250VDC	0.55

型号的解释:

AX □□ -3 0 -□□ -□□

控制线圈型号代码: 见表一

常开或者是常闭辅助触点对数: 10 为 1 对常开辅助触点;
01 为 1 对常闭辅助触点

常闭主触点对数 0: 0 对常闭主触点

常开主触点对数 3: 3 对常开主触点

380V 工作电压 AC-3 下额定工作电流(A)

0.7A; 0.9A; 1.2A; 1.5A; 1.8A; 2.5A

系列名称: AX 系列接触器



中国质量认证中心



产品认证证书

II型自愿认证

证书编号: CQC2013010304646608

第 3 页 共 3 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号: 105849

表一

额定工作电压 (Vac)		线圈代号
50Hz	60Hz	
24	24	81
48	48	83
105	110-127	26
110	110-120	84
190	220	36
200	200-220	75
220-230	230-240	80
230-240	240-260	88
380-400	400-415	85
400-415	415-440	86



中国质量认证中心

