## Fusible disconnect switches OS60 and OS100 Gamma range

OS Gamma fusible disconnect switches ensure safe operation, protecting both people and equipment even in extreme conditions.



#### **Designed for safety**

Designed and based on substantial experience of electrical safety, OS Gamma fusible disconnect switches eliminate the risk of electrical accidents:

- The interlocking fuse covers prevent opening while the fusible switch is in the ON-position and can be sealed in the closed position.
- Double insulated external operating handle that eliminates the risk of touching live parts outside the box.
- Reliable contact position indication in all situations.
- Frame made of robust plastic, with excellent mechanical and thermal properties.
- Voltage output pins as standard.
- Pole markings as standard.
- You take no risks with OS Gamma range.

#### Superior performance

- Smart design, with optimal contact constructions.
- High insulation ratings
- OS Gamma fusible disconnect switches meet the requirements to be installed close to the main transformer: up to 200 kA in heavy industry and in ships.
  - Suitable for all applications in low voltage networks

- Adjustable mounting feet that allow top and side mounting.
- Mounting the cables is simple thanks to high terminal positioning with space to the back plate. This is also ideal for double cabling, which in turn saves space.
  - Flexible and time-saving installation

#### Compact construction

- An intelligent construction in combination with a small number of components results in a very compact mechanism design.
- Very small footprint area.
  - Space savings mean cost reduction

A wide selection of accessories improves the usability of the fusible switches.

# Fusible disconnect switches - OS60 and OS100 Gamma range Ordering information / Technical data

## Ordering information



Catalog number	Number of poles	Weight/ unit [kg]
OS60GJ03	3	1.3
OS60GJ12	3	1.3
OS60GJ04F	4	1.8
OS60GJ22F	4	1.8
OS100GJ03	3	2.2
OS100GJ12	3	2.2
OS100GJ04F	4	2.7
OS100GJ22F	4	2.7

## Accessories

## **Auxiliary Contacts**

Item	Catalog number
1NC	OA1G10*
1NO	OA3G01*
Auxiliary contact module	OEA28

\* Add suffix "AU" for gold contacts

### Lugs

Item	Catalog number
OS100G	OZXA-24

## **Direct mount handles**

ltem	Catalog number	
OS60G & OS100G	OSV200BK	

## **DIN** rail adapter

Item	Catalog number
OS60G & OS100G	OSGZD1

## Technical data


Technical data according to UL/ <sub>C</sub> UL <sub>US</sub>			Α	OS 60G	OS 100G
General purpose amp rating		-40° to 40 °C	А	60	100
Max. operating voltage			VAC	600	600
iviax. operating voltage			VDC	250	250
Marilla and a second second		240 V	HP/A	15/42.0	30/80.0
Max. horsepower rating / motor FLA current		480 V	HP/A	30/40.0	60/77.0
1 B ( odiron		600 V	HP/A	50/52.0	75/77.0
			kA	200	200
Short circuit rating with fuse, 3 and 4-pole types	UL/CSA fuse size		А	60	100
	UL/CSA fuse type			J	J
Min. electrical endurance	pf= 0.750.8	operation cycles		6000	6000
Mechanical endurance		operation cycles		20000	20000
Terminal lug kits				Integral	OZXA-24
Wire range			AWG	#14-4	#14-2/0
Torque	Wire tightening		lb.in	30/35 1)	120
Torque	Lug mounting		lb.in	N/A	50

<sup>1) 30</sup> lb.in with cable size #14-10, 35lb.in with cable size #8-4

## Fusible disconnect switches - OS60 and OS100 Gamma range Dimension drawings


### OS60G\_03-04

	J03 [mm/in]	J04 [mm/in]
A	144.5/5.69	179.5/7.07
В	118/4.65	118/4.65
С	35/1.38	35/1.38
D	45.5/1.79	45.5/1.79
E	36/1.41	36/1.41
A1	121/4.76	156/6.14
B1	151/5.94	186/7.32



### OS60G\_12-22


	J12 [mm/in]	J13 [mm/in]	J22 [mm/in]
A	109.5/4.31	144.5/5.69	179.5/7.07
В	118/4.65	118/4.65	118/4.65
С	35/1.38	35/1.38	35/1.38
D	45.5/1.79	45.5/1.79	45.5/1.79
E	36/1.41	36/1.41	36/1.41
A1	86/3.39	121/4.76	156/6.14
B1	116/4.57	151/5.94	186/7.32



## Fusible disconnect switches - OS60 and OS100 Gamma range Dimension drawings

#### OS100G\_03-04

	J03	J04
	[mm/in]	[mm/in]
Α	146.5/5.77	181.5/7.15
A1	125/4.92	160/6.30
B1	140/5.51	175/6.89
C1	155/6.10	190/7.48



#### OS100G 12-22

	J12 [mm/in]	J13 [mm/in]	J22 [mm/in]
A	148/5.83	183/7.20	183/7.20
В	81/3.19	81/3.19	116/4.57
A1	125/4.92	160/6.30	160/3.15
A2	71.5/2.81	45/1.77	80/3.15
B1	45/1.77	175/6.89	175/6.89
B2	52.5/2.07	52.5/2.07	160/3.44
C1	155/6.10	190/7.48	190/7.48
C2	60/2.36	60/2.36	95/3.74

### ABB Inc.

Low Voltage Control Products 16250 W. Glendale Drive New Berlin, WI 53151 Phone: 888-385-1221

Fax: 800-726-1441

USA Technical support & Customer Service:

888-385-1221, Option 4 7:30AM to 5:30PM, CST,

Monday - Friday

lvps.support@us.abb.com

Web: www.abb.us/lowvoltage

