# Safety Interlock Switch MKey9









## Application:

- Gates
- Hatches

### Features:

- Compact and robust
- 8 actuating positions
- High holding force
- Up to PL e/Cat.4
- LED status indication

#### Switch operational description

The MKey9 interlock safety switches are design to provide position interlock detection and locking for moving guards. They are designed to fit the leading edge of sliding, hinged or lift off machine guards. The actuator is fitted to the moving part of the guard and is aligned to the switch entry aperture. The possibility to lock the switch in the protective position prevents unwanted access to machinery until dangerous operations have ceased.

The locking is useful when applications include:

- processes which cannot be interrupted, such as welding.
- machinery with a long stopping procedure, such as paper machinery, that requires a long braking operation.
- prevention of unauthorised access to a particular area.

The head can be set in four positions, thus providing the safety device with eight different operating positions. The leading edges of the actuator key are reinforced and bevelled in order to guide it properly into the hole. The safety switch is design to have a high holding force of 2000N. MKey9 has several types of actuators as an option. A standard actuator key is always delivered with interlock switches.

#### Material

The MKey9 is made in a rugged polyester housing with a stainless steel head which give the switch a rating of IP67.

#### Two versions

The MKey9 is available in two basic versions, either with a spring lock or an electro-magnetic lock.

In the spring lock version, the locking mechanism moves into the locked position directly when the door is closed and the actuator key is pushed into the switch. The actuator key can only be released and the gate opened by supplying operational voltage to the solenoid (A1-A2).

MKey9M is the electro-magnetic lock version, the locking mechanism is in the locked position when the solenoid (A1-A2) is supplied with operating voltage. Release of the actuator key is only possible when the operating voltage is removed from the solenoid (A1-A2). The solenoid voltage is 24VDC.

#### Safety level

The MKey9 has double forced disconnection contacts to the actuator key and the locking mechanism. The actuator key is designed to protect against unauthorised access; no tools, magnets or similar allow that the MKey9 can be tampered with. To achieve maximum safety level in connection with the machine control system, it is recommended that the MKey9 is monitored by an appropriate ABB Jokab Safety safety relay, Pluto safety-PLC or Vital system. To obtain the highest level of safety, two switches per gate are required.

#### **Regulations and Standards**

The MKey9 is designed and approved in accordance to relevant standards. Examples of relevant standards are EN 1088, IEC/EN 60947-5-1, EN 60204-1, EN ISO 13849-1, EN 62061 and UL 508.

Technical data - MKey9 seri	es			
Article number				
MKey9 - 24VDC	2TLA050007R0112			
MKey9M - 24VDC (power to lock)	2TLA050009R0112			
Level of Safety				
EN ISO 13849-1	Up to PL e/Cat. 4 depending upon			
	system architecture			
EN 62061	Up to SIL3 depending upon system			
	architecture			
Safety data				
Mechanical reliability B <sub>10d</sub>	2,5 x 10 <sup>6</sup> operations at 100mA load			
	35 years			
Proof test interval (life)	356 years (8 cycles per hour/24			
MTTF <sub>d</sub>	hours per day/365 days)			
Utilisation category	AC15 A300 3A			
Solenoid voltage	24 VDC or 230 VAC, +/- 10%			
Solenoid power consumption				
MKey9	12 W			
MKey9M	12 W (Inrush 50W)			
LED 2 supply voltage	24 VDC, +/- 10%			
Travel for positive opening	10 mm			
Actuator entry mini. radius	175 mm Standard Key			
	100 mm Flexible Key			
Max. approached/withdrawal speed	600 mm/s			
Rated insulation/withstand voltages	600VAC / 2500VAC			
Vibration resistance	IEC 68-2-6, 10-55 Hz+ 1 Hz			
	excursion: 0.35 mm			
	1 octave/min.			
Thermal current (Ith)	5A			
Conduit entry	1 x M20			
Enclosure classification	IP67			
Operating temperature	<u>.</u>			
MKey9	-25°C to +55°C			
MKey9M	-25°C to +40°C			
Head/body material	Stainless steel 316/polyester			
Colour	Red			
Mounting position	Any			
Mounting bolts	4 x M5			
	1 / 1410			




#### Actuator


- 1. Standard Key for SS head
- 2. Flat Key
- 3. Flexible Key with metal housing
- 4. Flexible Key with SS housing (Key always in Stainless steel)

2TLA050040R0202 2TLA050040R0220 2TLA050040R0203 2TLA050040R0204





Schematic circuit MKey9 LED1 status of solenoid LED2 status of lock (Terminals 33 - 34 are selectable to be used either as power feed to LED2  $\,$ or as a voltage free auxiliary circuit to indicate lock status).



Dimensions MKey9 and MKey9M

	6.0	) 5	5.0		<u>0 m</u> n
11/12	Open			Solenoid energised	
21/22	Open			Solenoid energised	
33/34	Open			Tongue Inserted	
43/44		Оре	en	Tongue Inserted	

MKey9M, Contacts at withdrawal of actuator.

	6.0	) {	5.0		0 n	nm
11/12	Open					
21/22	Open					
33/34				Open		
43/44				Open		

MKey9, Contacts at withdrawal of actuator.