


FurseWELD

Bar to bar BB1

Bar to bar BB1 - FurseWELD



| Flat tape conductor size A (mm) | Mould part no. | Order code | Powder cartridge part no. | Handle clamp part no. |
|---------------------------------|----------------|-----------------|---------------------------|-----------------------|
| 20 x 3 | BB1-4-203 | 7TCA083910R2736 | 45P10 | HCPK4 |
| 25 x 3 | BB1-4-253 | 7TCA083910R0007 | 65P10 | HCPK4 |
| 25 x 4 | BB1-4-254 | 7TCA083910R0010 | 90P10 | HCPK4 |
| 25 x 6 | BB1-4-256 | 7TCA083910R0011 | 150P10 | HCPK4 |
| 30 x 3 | BB1-4-303 | 7TCA083910R0013 | 90P10 | HCPK4 |
| 30 x 4 | BB1-4-304 | 7TCA083910R0015 | 115P10 | HCPK4 |
| 30 x 5 | BB1-4-305 | 7TCA083910R0016 | 115P10 | HCPK4 |
| 31 x 6 | BB1-4-316 | 7TCA083910R0019 | 150P10 | HCPK4 |
| 38 x 5 | BB1-4-385 | 7TCA083910R0021 | 150P10 | HCPK4 |
| 38 x 6 | BB1-4-386 | 7TCA083910R0022 | 200P10 | HCPK4 |
| 40 x 3 | BB1-4-403 | 7TCA083910R0023 | 115P10 | HCPK4 |
| 40 x 4 | BB1-4-404 | 7TCA083910R0024 | 150P10 | HCPK4 |
| 40 x 5 | BB1-4-405 | 7TCA083910R0027 | 150P10 | HCPK4 |
| 40 x 6 | BB1-4-406 | 7TCA083910R0028 | 200P10 | HCPK4 |
| 50 x 3 | BB1-4-503 | 7TCA083910R0030 | 150P10 | HCPK4 |
| 50 x 4 | BB1-4-504 | 7TCA083910R0031 | 200P10 | HCPK4 |
| 50 x 5 | BB1-4-505 | 7TCA083910R0032 | 200P10 | HCPK4 |
| 50 x 6 | BB1-4-506 | 7TCA083910R0033 | 250P10 | HCPK4 |

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

Conductors must be installed in the orientation shown to achieve the correct connection