

V_{DM}	=	5200 V
$I_{T(AV)M}$	=	1800 A
$I_{T(RMS)}$	=	2830 A
I_{TSM}	=	29×10^3 A
V_{TO}	=	1.02 V
r_T	=	0.32 mW

Bi-Directional Control Thyristor

5STB 17N5200


Doc. No. 5SYA1036-04 May 07

- Two thyristors integrated into one wafer
- Patented free-floating silicon technology
- Designed for energy management and industrial applications
- Optimum power handling capability
- Interdigitated amplifying gate

The electrical and thermal data are valid for one-thyristor-half of the device (unless otherwise stated)

Blocking

Maximum rated values¹⁾

Parameter	Symbol	Conditions	5STB 17N5200	Unit
Max. surge peak forward blocking voltage	V_{SM}	$t_p = 10$ ms, $f = 5$ Hz $T_{vj} = 5 \dots 125^\circ\text{C}$, Note 1	5200	V
Max repetitive peak forward blocking voltage	V_{RM}	$f = 50$ Hz, $t_p = 10$ ms, $t_{p1} = 250$ μs , $T_{vj} = 5 \dots 125^\circ\text{C}$, Note 1	5200	V
Max crest working forward voltages	V_{WM}		2600	V
Critical rate of rise of off-state voltage	dv/dt_{crit}	Exp. to 2950 V, $T_{vj} = 125^\circ\text{C}$	2000	$\text{V}/\mu\text{s}$

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Max reverse leakage current	I_{RM}	V_{RM} , $T_{vj} = 125^\circ\text{C}$			400	mA

Note 1: Voltage de-rating factor of 0.11% per $^\circ\text{C}$ is applicable for T_{vj} below $+5^\circ\text{C}$

Note 2: Recommended minimum ratio of V_{DRM} / V_{DWM} or $V_{RRM} / V_{RWM} = 2$. See App. Note 5SYA 2051.

Mechanical data

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Mounting force	F_M		81	90	108	kN
Acceleration	a	Device unclamped			50	m/s^2
Acceleration	a	Device clamped			100	m/s^2

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Weight	m				2.9	kg
Housing thickness	H	$F_M = 90$ kN, $T_a = 25^\circ\text{C}$	34.8		35.4	mm
Surface creepage distance	D_S		53			mm
Air strike distance	D_a		22			mm

1) Maximum rated values indicate limits beyond which damage to the device may occur

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



On-state

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Average on-state current	I _{T(AV)M}	Half sine wave, T _c = 70 °C			1800	A
RMS on-state current	I _{T(RMS)}				2830	A
RMS on-state current	I _{T(RMS)}	Full sine wave, T _c = 70 °C t _p = 10 ms, T _{vj} = 125 °C, sine wave after surge: V _D = V _R = 0 V			4000	A
Peak non-repetitive surge current	I _{TSM}				29.0×10 ³	A
Limiting load integral	I ² t	t _p = 8.3 ms, T _{vj} = 125 °C, sine wave after surge: V _D = V _R = 0 V			4.21×10 ⁶	A ² s
Peak non-repetitive surge current	I _{TSM}				31.0×10 ³	A
Limiting load integral	I ² t				3.99×10 ⁶	A ² s

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
On-state voltage	V _T	I _T = 2000 A, T _{vj} = 125 °C			1.68	V
Threshold voltage	V _{T0}	I _T = 1000 A - 3000 A, T _{vj} = 125 °C			1.02	V
Slope resistance	r _T				0.32	mΩ
Holding current	I _H	T _{vj} = 25 °C	50		250	mA
		T _{vj} = 125 °C			150	mA
Latching current	I _L	T _{vj} = 25 °C			500	mA
		T _{vj} = 125 °C			300	mA

Switching

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Critical rate of rise of on-state current	di/dt _{crit}	T _{vj} = 125 °C, I _{TRM} = 3000 A, f = 50 Hz			250	A/μs
Critical rate of rise of on-state current	di/dt _{crit}				500	A/μs
Circuit commutated turn-off time	t _q	T _{vj} = 125 °C, I _{TRM} = 2000 A, V _R = 200 V, di _T /dt = -1.5 A/μs, V _D ≤ 0.67·V _{RM} , dv _D /dt = 20 V/μs	700			μs
Critical rate of rise of commutating voltage	dv/dt _{com}	T _{vj} = 125 °C, V _R ≤ 0.67·V _{RM}			500	V/μs

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Reverse recovery charge	Q _{rr}	T _{vj} = 125 °C, I _{TRM} = 2000 A, V _R = 200 V, di _T /dt = -1.5 A/μs	3500		6500	μAs
Reverse recovery current	I _{RM}		65		90	A
Gate turn-on delay time	t _{gd}	T _{vj} = 25 °C, V _D = 0.4·V _{RM} , I _{FG} = 2 A, t _r = 0.5 μs			3	μs

Triggering

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Peak forward gate voltage	V_{FGM}				12	V
Max. rated peak forward gate current	I_{FGM}				10	A
Peak reverse gate voltage	V_{RGM}				10	V
Max. rated gate power loss	P_G	For DC gate current			3	W
Max. rated peak forward gate power	$P_{GM(AV)}$			see Fig. 9		W

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Gate trigger voltage	V_{GT}	$T_{vj} = 25^\circ C$			2.6	V
Gate trigger current	I_{GT}	$T_{vj} = 25^\circ C$			400	mA
Gate non-trigger voltage	V_{GD}	$V_D = 0.4 \times V_{RM}, T_{vj} = 125^\circ C$	0.3			V
Gate non-trigger current	I_{GD}	$V_D = 0.4 \times V_{RM}$	10			mA

Thermal

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Operating junction temperature range	T_{vj}				125	°C
Storage temperature range	T_{stg}		-40		140	°C

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Thermal resistance junction to case (Valid for one thyristor half no heat flow to the second half.)	$R_{th(j-c)}$	Double-side cooled $F_m = 81...108 \text{ kN}$			11.4	K/kW
	$R_{th(j-c)}$	Single-side cooled $F_m = 81...108 \text{ kN}$			22.8	K/kW
Thermal resistance case to heatsink	$R_{th(c-h)}$	Double-side cooled $F_m = 81...108 \text{ kN}$			2	K/kW
	$R_{th(c-h)}$	Single-side cooled $F_m = 81...108 \text{ kN}$			4	K/kW

Analytical function for transient thermal impedance:

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/t_i})$$

i	1	2	3	4
$R_i(\text{K/kW})$	6.770	2.510	1.340	0.780
$\tau_i(\text{s})$	0.8651	0.1558	0.0212	0.0075








Fig. 1 Transient thermal impedance (junction-to-case) vs. time







On-state characteristic model:

$$V_{T\max} = A + B \cdot I_T + C \cdot \ln(I_T + 1) + D \cdot \sqrt{I_T}$$

Valid for $I_T = 500 - 4000$ A

A	B	C	D
1.309	80.0×10^{-6}	-125.0×10^{-3}	26.0×10^{-3}

 I_T (kA)**Fig. 2** On-state characteristics,
 $T_j = 125^\circ\text{C}$, 10ms half sine**Fig. 3** On-state voltage characteristics**Fig. 4** On-state power dissipation vs. mean on-state current. Turn-on losses excluded.**Fig. 5** Max. permissible case temperature vs. mean on-state current. Switching losses ignored.



Turn-on and Turn-off losses




Fig. 12 Turn-on energy, half sinusoidal waves




Fig. 13 Turn-on energy, rectangular waves




Fig. 14 Turn-off energy, half sinusoidal waves




Fig. 15 Turn-off energy, rectangular waves




Fig. 16 Current and voltage waveforms at turn-off

Total power loss for repetitive waveforms:

$$P_{TOT} = P_T + W_{on} \cdot f + W_{off} \cdot f$$

where

$$P_T = \frac{1}{T} \int_0^T I_T \cdot V_T(I_T) dt$$

Fig. 17 Relationships for power loss




Fig. 18 Device Outline Drawing

Related documents:

-
- | | |
|-----------|---|
| 5SYA 2020 | Design of RC-Snubber for Phase Control Applications |
| 5SYA 2049 | Voltage definitions for phase control thyristors and diodes |
| 5SYA 2051 | Voltage ratings of high power semiconductors |
| 5SYA 2034 | Gate-Drive Recommendations for PCT's |
| 5SYA 2036 | Recommendations regarding mechanical clamping of Press Pack High Power Semiconductors |
| 5SZK 9104 | Specification of environmental class for pressure contact diodes, PCTs and GTO, STORAGE available on request, please contact factory |
| 5SZK 9105 | Specification of environmental class for pressure contact diodes, PCTs and GTO, TRANSPORTATION available on request, please contact factory |

Please refer to <http://www.abb.com/semiconductors> for current version of documents.

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



**ABB Switzerland Ltd
Semiconductors**
Fabrikstrasse 3
CH-5600 Lenzburg, Switzerland

Doc. No. 5SYA1036-04 May 07

Telephone +41 (0)58 586 1419
Fax +41 (0)58 586 1306
Email abbsem@ch.abb.com
Internet www.abb.com/semiconductors