

TECHNICAL DATA SHEET

# **Data & Signal Protection**

ESP RS485, SRS485, RS485Q & Slimline RS485 Series



Combined Category D, C, B tested (to IEC/BS EN 61643) Surge Protection Device (SPD) specifically designed for RS 485 and Fieldbus applications, such as Profibus DP. For use at boundaries up to LPZ 0 protect against flashover (typically the service entrance location) through to LPZ 3. Available as standard ESP RS485 format, slim ESP SRS485 format or compact ESP RS485Q and Slim Line ESP SL RS485 versions for installations where a high number of lines require protection.



- · Very low let-through voltage (enhanced protection to IEC/BS EN 62305) between all lines - Full Mode protection
- Full Mode design capable of handling partial lightning currents as well as allowing continual operation of protected equipment
- Repeated protection in lightning intense environments
- 45 MHz bandwidth greatly exceeds 12 Mbps maximum speeds
- Low in-line resistance minimizes reductions in signal strength
- Suitable for earthed or isolated screen systems
- Built-in DIN rail foot for simple mounting to top hat DIN rails
- Convenient earthing through DIN foot and/or earth terminal
- Connect screen connection 'S' as the 0V ground on RS485 systems
- ESP RS485 can be flat mounted on base or side
- ESP RS485, ESP SRS485 and ESP RS485Q have colour coded terminals for quick and easy installation check

## **Application**

From line

Connect in series with the signal line either near where it enters or leaves the building or close to the equipment being protected ensuring it is very close to the system's earth star point. Install SPDs either within an existing cabinet/ cubicle or in a separate enclosure.

To equipment




























- ESP SRS485 (6.2 mm) and ESP SL RS485 (7 mm) are ultra slim units, ideal for compact protection of large numbers of lines (e.g. process control installations)
- ESP SL RS485 includes two stage removable protection module with simple quick release mechanism allowing partial removal for easy line commissioning and maintenance as well as full removal for protection replacement
- ESP SL RS485 includes optional LED status indication. Add L suffix to part number - i.e. ESP SL RS485L
- · ESP SRS485 has LED status indication as standard
- ESP SRS485 and ESP RS485Q available with Push Terminals (ESP SRS485/PT and ESP RS485Q/PT) for simple 'spring' connections, to provide fast and reliable cable termination
- ESP RS485Q(UL), ESP RS485Q/PT(UL), ESP SLRS485(UL) and ESP SLRS485L(UL) have UL497B approval under file E240341

#### Accessories

For replacement SPD modules (/M), spare base units (/B), weatherproof enclosures (WBX) and combined mounting and earthing kits (CME) see ABB order code table overleaf.


Combined Mounting/ Earthing kits for ESP RS485: **CME 4** (upto 4 x ESP RS485) **CME 8** (upto 8 x ESP RS485) **CME 16** (upto 16 x ESP RS485) CME 32 (upto 32 x ESP RS485)

## ESP SRS485 installed in series




Earth

## ESP SL RS485 installed in series



## ESP RS485Q installed in series



To equipment

NOTE: The ESP SL 'Slim Line' Series is also available for protection of 3-wire and RTD applications (ESP SL/3W & ESP SL RTD). The ESP SL X Series has approvals for use in hazardous areas.

Electrical specification	ESP RS485	ESP SL RS485	ESP RS485Q	ESP SRS485
Nominal voltage <sup>(1)</sup>	15 V			
Maximum working voltage $U_{\rm c}$ (DC) $^{(2)}$	16.7 V			
Maximum working voltage <i>U</i> c (AC RMS)	11 V			
Current rating (signal)	300 mA			
n-line resistance (per line ±10%)	1Ω			
Bandwidth (-3 dB 50 Ω system)	45 MHz			
Transient specification		,		
Let-through voltage (all conductors) <sup>(3)</sup> <i>U</i> p				
C2 test 4 kV 1.2/50 μs, 2 kA 8/20 μs to BS EN/EN/IEC 61643-2	21 55.0 V			
C1 test 1 kV, 1.2/50 μs, 0.5 kA 8/20 μs to BS EN/EN/IEC 61643	3-21 42.0 V			
B2 test 4 kV 10/700 μs to BS EN/EN/IEC 61643-21	27.2 V			
5 kV, 10/700 μs <sup>(4)</sup>	28.2 V			
Maximum surge current		,		
D1 test 10/350 μs to – Per signal wire 2.5 kA	2.5 kA	1.25 kA	2.5 kA	2.5 kA
BS EN/EN/IEC 61643-21: – Per pair	5 kA	2.5 kA	5 kA	5 kA
8/20 µs to ITU-T K.45:2003, — Per signal wire IEEE C62.41.2:2002: — Per pair	10 kA 20 kA	5 kA 10 kA	10 kA 20 kA	10 kA 20 kA
Mechanical specification		10.101		20.01
Temperature range	-40 to +80 °	°C		1
Connection type	Screw term max. torque 0.5 Nm	ninal - Screw terminal -	Pluggable 12 was screw terminal	ay Screw terminal - max torque 0.4 Nm /PT version: Pluggable screwless Push Termina
Conductor size (stranded)	2.5 mm²	4 mm²	2.5 mm²	2.5 mm²
Earth connection	M6 stud	Via DIN rail or 4 r earth terminal - max. torque 0.8 l	M5 threaded ho	Via DIN rail earth or le earth terminal
Case Material	FR Polymer	r UL-94 V-0		
Weight: – Unit	0.08 kg			
Dimensions	See diagrar	ms below		
(3) Nominal voltage (DC or AC peak) measured at < 10 μA (22) Maximum working voltage (DC or AC peak) measured at < 5 mA (33) The maximum transient voltage let-through of the protectorthroughout the test (±10%), line to line & line to earth, both polarities. Response time < 10 ns (43) Test to IEC 61000-4-5:2006, ITU-T (formerly CCITT) K.20, K.21 and K.45,Telcordia GR-1089-CORE, Issue 2:2002, ANSI TIA/EIA/IS-968-A:2002 (formerly FCC Part 68)	ESP RS485	105 mm M4 clearance	## ESP RS485Q	95 mm (*)  O  M3 clearance Depth: 18 mm  O  O  O  O  O  O  O  O  O  O  O  O
ESP SRS485	19 mm O	120 mm  109 mm  M4 clearance	ESP SL RS485	* Q/PT width is 106 mm
91	- - -	7 mm		furse of f

ABB order codes						
Part no.	ABB order code	Part no.	ABB order code	Part no.	ABB order code	
ESP RS485	7TCA085400R0191	ESP RS485Q	7TCA085400R0192	CME16	7TCA085410R0002	
ESP SLRS485/B	7TCA085400R0262	ESP RS485Q(UL)	7TCA085400R0558	CME32	7TCA085410R0003	
ESP SLRS485	7TCA085400R0193	ESP RS485Q/PT	7TCA08540OR0475	WBXSLQ	7TCA085410R0037	
ESP SLRS485L	7TCA085400R0230	ESP RS485Q/PT(UL)	7TCA085400R0565	WBXSLQ/G	7TCA085410R0036	
ESP SLRS485(UL)	7TCA085400R0525	ESP SLRS485/M	7TCA085400R0259	WBX 4	7TCA085410R0027	
ESP SLRS485L(UL)	7TCA085400R0526	ESP SLRS485L/M	7TCA085400R0471	WBX 8	7TCA085410R0030	
ESP SRS485	7TCA085400R0629	CME4	7TCA085400R0001	WBX 16/2/G	7TCA085410R0020	
ESP SRS485/PT	7TCA085400R0647	CME8	7TCA085400R0002			