

Exit LED Quickfit® Signature exit LED Quickfit weatherproof



Range


Signature range

Product group

Exit LED Quickfit®

Features

- 3 year warranty
- LED technology 100,000 hours lamp life
- IP65 weatherproof enclosure
- Advanced pulsetime dual rate battery charger with high temperature NiCad batteries
- Quickfit® unique steel slide connect bracket for quick installation and easy maintenance
- UV stabilised vandal resistant polycarbonate cover or high impact chemical resistant acrylic cover option
- Can be wall or ceiling mounted and optional bracket kits available for strengthened wall and cantilever mounting



Standard products

Catalogue no.	Description
PWQFLEDP-1	LED Quickfit weatherproof SS polycarbonate picto exit
PWQFLEDP-2	LED Quickfit weatherproof SS polycarbonate <picto exit
PWQFLEDP-3	LED Quickfit weatherproof SS polycarbonate picto> exit
PWQFLEDP-5	LED Quickfit weatherproof DS polycarbonate picto exit
PWQFLEDP-6	LED Quickfit weatherproof DS polycarbonate picto AOW exit
PWQFLEDA-1	LED Quickfit weatherproof SS acrylic picto exit
PWQFLEDA-2	LED Quickfit weatherproof SS acrylic <picto exit
PWQFLEDA-3	LED Quickfit weatherproof SS acrylic picto> exit
PWQFLEDA-5	LED Quickfit weatherproof DS acrylic picto exit
PWQFLEDA-6	LED Quickfit weatherproof DS acrylic picto AOW exit

Accessories

Catalogue no.	Description
WQFCLH	Cantilever mounting bracket - heavy duty
WQFCLL	Cantilever mounting bracket - light duty
WQFWM	Wall mount bracket

Spare parts

Catalogue no.	Description
03-01218	Battery 4 cell NiCad 4.8V 1.8Ah

Dimensions

Length	Width	Height
466mm	155mm	274mm

Weight

Model	Weight
Standard	3.6kg

Construction

Part	Construction
Body	Black UV/FR polycarbonate
Diffuser	Opal acrylic
Bracket	Black powder coated zinc steel
Enclosure cover	UV polycarbonate or high impact acrylic
Enclosure base	Black glass reinforced UV stabilised nylon

Light source

Model	Light source
Standard	Multiple LED 1.6W

Power consumption

Model	Power consumption
Standard	3.6W

Photometrics

Model	Class	Classification
Standard	C0	D3.2
	C90	D3.2

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

ABB Australia Pty Limited

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

Note: We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2017 ABB
All rights reserved