



EMERGI-LITE

Guideway & Serenga 2

Escape route signalisation and
escape route lighting

Guideway & Serenga 2

Escape route signalisation and escape route lighting


Guideway escape route signalisation blends the finest in pictogram illumination with minimalistic design. The uniformly illuminated pictogram plate is clearly visible in daylight with a light intensity of 500 cd/m². The frameless pictogram plate with its minimalistic metal design ensures a fluent transition between signalisation and surroundings. In conjunction with Serenga 2, Guideway provides you with a range of project-covering emergency lighting. The futuristic design combines the highest degree of operational reliability with specific lighting for corridors, open spaces as well as stairwells.



Watch the video


Guideway Easy to install

Versatile mounting options




Guideway Increased safety

Clearly visible in daylight



Guideway Focus on design

In harmony with
interior spaces






Guideway escape route signalisation

Light power surrounded by frameless design

Frameless
legend design


Versatile
mounting options



Watch the video


Guideway Increased safety

Uniform light distribution




Guideway Focus on design

Frameless legend design



Guideway Streamlined range

Viewing distance



Guideway escape route signalisation

Installation in focus

01 Surface
mounted 22 metres
Watch the video



02 Recessed 22 metres
Watch the video



03 Surface mounted
32 metres wall model
Watch the video



04 Recessed
replacement pictogram
Watch the video



05 Surface mounted
22 metres First-Fix
control gear
Watch the video



06 Surface mounted
32 m wall model
First-Fix control gear
Watch the video




07 Surface mounted
replacement battery
Watch the video



08 Recessed
replacement battery
Watch the video



01



02




03




04



05



06



07



08


Guideway

Innovative & stylish



Guideway 22m - Recessed

- Clearly visible in daylight - 500 cd/m²
- Uniform light distribution
- In harmony with interior spaces
- Frameless legend design



Luminaire

Order code	Description	Input voltage	Lamp type	Power consumption / duration		Environment temp. (°C)	Weight (kg)	Including
				(mA)	(hrs)			
CTEGR3LS1-S22	REC LED SIGN M3 CT-TST 22M	220-240 AC 50Hz	1 x LED	18.3	3	5-35	1.2	
EGR1LS1D-S22	REC LED SIGN 230DIM 22M	220-240 AC/DC 0-60Hz			230V	0-35	1.2	
EGR1LS1LTC-S22	REC LED SIGN SLAVE LTC 230VAC 22M	220-240 AC 50/60 Hz			230V	0-35	1.2	
EGR1LS1-S22	REC LED SIGN SLAVE 230VAC 22M	220-240 AC/DC 0-60Hz			230V	0-35	1.2	
EGR3LS1-S22	REC LED SIGN M3 22M	220-240 AC 50Hz			3	5-35	1.2	
DAEGR3LS1-S22	REC LED SIGN M3 22M DALI	220-240 AC 50Hz			3	5-35	1.2	

'60Hz' option available on request, please contact ABB. Designed and manufactured to meet the requirements of BS EN 60598.2.22.

Single sided

Part No.	Legends
ISO 7010 legend format	
XEN2EG22	
XEN3EG22	
XEN6EG22	
XEN5EG22	
Arabic legend format	
XBN1EG22	

ISO 7010 pictogram legends are shown. Euro format & Special legends are available to order.

Flag mounted

Part No.	Legends
ISO 7010 legend format	
XEN602EG32	
XEN603EG32	
XEN606EG32	
XEN605EG32	






Accessories

Order code	Description	Colour
EG-T4SG	Cover discs, 2+2 self contained	
EG-T4EG	Cover discs, 2+2 slave	

Suspension kit accessories


Order code	Description
EG-TKIT50	Pendant 500
EG-TKIT100	Pendant 1000
EG-WKIT150	Wire suspension kit



Guideway
Innovative & stylish



- Guideway 32m - Recessed**
- Clearly visible in daylight - 500 cd/m²
 - Uniform light distribution
 - In harmony with interior spaces
 - Frameless legend design



Luminaire

Order code	Description	Input voltage	Lamp type	Power consumption / duration		Environment temp. (°C)	Weight (kg)	Including
				(mA)	(hrs)			
CTEGR3LS1-S32	REC LED SIGN M3 CT-TST 32M	220-240 AC 50Hz	1 x LED	18.3	3	5-35	1.5	
EGR1LS1D-S32	REC LED SIGN SLAVE 230DIM 32M	220-240 AC/DC 0-60Hz			230V	0-35	1.5	
EGR1LS1LTC-S32	REC LED SIGN SLAVE LTC 230 VAC 32M	220-240 AC 50/60 Hz			230V	0-35	1.5	
EGR1LS1-S32	REC LED SIGN SLAVE 230 VAC 32M	220-240 AC/DC 0-60Hz			230V	0-35	1.5	
EGR3LS1-S32	REC LED SIGN M3 32M	220-240 AC 50Hz			3	5-35	1.5	
DAEGR3LS1-S32	REC LED SIGN M3 32M DALI	220-240 AC 50Hz			3	5-35	1.5	

'60Hz' option available on request, please contact ABB. Designed and manufactured to meet the requirements of BS EN 60598.2.22.

Single sided

Part No.	Legends
ISO 7010 legend format	
XEN2EG32	
XEN3EG32	
XEN6EG32	
XEN5EG32	
Arabic legend format	
XBN1EG32	

ISO 7010 pictogram legends are shown.
Euro format & Special legends are available to order.

Flag mounted

Part No.	Legends
ISO 7010 legend format	
XEN602EG22	
XEN603EG22	
XEN606EG22	
XEN605EG22	




Accessories

Order code	Description	Colour
EG-T4SG	Cover discs, 2+2 self contained	
EG-T4EG	Cover discs, 2+2 slave	


Suspension kit accessories

Order code	Description
EG-TKIT50	Pendant 500
EG-TKIT100	Pendant 1000
EG-WKIT150	Wire suspension kit




Guideway

Innovative & stylish



Guideway 22m - Surface

- Clearly visible in daylight - 500 cd/m²
- Uniform light distribution
- In harmony with interior spaces
- Frameless legend design



Luminaire

Order code	Description	Input voltage	Lamp type	Power consumption / duration		Environment temp. (°C)	Weight (kg)	Including
				(mA)	(hrs)			
CTEG3LS1-S22	LED SIGN M3 CT-TST 22M	220-240 AC 50Hz	1 x LED	18.3	3	5-35	1.5	
EG1LS1D-S22	LED SIGN SLAVE 230VAC DIM 22M	220-240 AC/DC 0-60Hz			230V	0-35		
EG1LS1LTC-S22	LED SIGN SLAVE LTC 230VAC 22M	220-240 AC 50/60 HZ			230V	0-35		
EG1LS1-S22	LED SIGN SLAVE 230VAC 22M	220-240 AC/DC 0-60Hz			230V	0-35		
EG3LS1-S22	LED SIGN M3 22M	220-240 AC 50Hz			3	5-35		
DAEG3LS1-S22	LED SIGN M3 22M DALI	220-240 AC 50Hz			3	5-35		

Includes back to wall mounting accessory as standard. '60Hz' option available on request, please contact ABB.
Designed and manufactured to meet the requirements of BS EN 60598.2.22.

Single sided

Part No.	Legends
ISO 7010 legend format	
XEN2EG22	
XEN3EG22	
XEN6EG22	
XEN5EG22	
Arabic legend format	
XBN1EG22	

ISO 7010 pictogram legends are shown.
Euro format & Special legends are available to order.


Flag mounted

Part No.	Legends
ISO 7010 legend format	
XEN602EG32	
XEN603EG32	
XEN606EG32	
XEN605EG32	




Accessories

Order code	Description
EG-TKIT50	Pendant 500
EG-TKIT100	Pendant 1000
EG-WKIT150	Wire suspension kit




Guideway

Innovative & stylish



- Guideway 32m - Surface**
- Clearly visible in daylight - 500 cd/m²
 - Uniform light distribution
 - In harmony with interior spaces
 - Frameless legend design



Luminaire

Order code	Description	Input voltage	Lamp type	Power consumption / duration		Environment temp. (°C)	Weight (kg) including
				(mA)	(hrs)		
CTEG3LS1-S32	LED SIGN M3 CT-TST 32M	220-240 AC 50Hz	1 x LED	18.3	3	5-35	1.6
EG1LS1D-S32	LED SIGN SLAVE 230VAC DIM 32M	220-240 AC/DC 0-60Hz			230V	0-35	
EG1LS1LTC-S32	LED SIGN SLAVE LTC 230VAC 32M	220-240 AC 50/60 Hz			230V	0-35	
EG1LS1-S32	LED SIGN SLAVE 230VAC 32M	220-240 AC/DC 0-60Hz			230V	0-35	
EG3LS1-S32	LED SIGN M3 32M	220-240 AC 50Hz			3	5-35	
DAEG3LS1-S32	LED SIGN M3 32M DALI	220-240 AC 50Hz			3	5-35	

Includes back to wall mounting accessory as standard. '60Hz' option available on request, please contact ABB.
Designed and manufactured to meet the requirements of BS EN 60598.2.22.

Single sided

Part No.	Legends
ISO 7010 legend format	
XEN2EG32	
XEN3EG32	
XEN6EG32	
XEN5EG32	
Arabic legend format	
XBN1EG32	

ISO 7010 pictogram legends are shown.
Euro format & Special legends are available to order.


Flag mounted

Part No.	Legends
ISO 7010 legend format	
XEN602EG22	
XEN603EG22	
XEN606EG22	
XEN605EG22	



Accessories


Order code	Description
EG-TKIT50	Pendant 500
EG-TKIT100	Pendant 1000
EG-WKIT150	Wire suspension kit






Serenga 2 Focus on design

In harmony with
interior spaces




Serenga 2 Increased safety

Escape route lighting
Long beam (L)
e.g. corridors



Serenga 2 Streamlined range

Wall model



Serenga 2 escape route lighting

The minimalistic way to maximum height

Up to
12 metres high



3 metres ceiling height,
23 metres spacing



Escape route lighting
Long beam (L)
e.g. corridors



In harmony with
interior spaces




Watch the video

Anti-panic lighting
Wide beam (W)
e.g. open area

Wall model

Serenga 2 Streamlined range

Up to 12 metres high




Serenga 2 Increased safety

Escape route lighting
Wide beam (W)
e.g. open area



Serenga 2 Project cost reduction

3 metres ceiling height,
23 metres spacing



Serenga 2 escape route lighting

Your benefits highlighted

01 Recessed
Watch the video



02 Surface mounted
Watch the video



03 Surface mounted
replacement battery
Watch the video



04 Recessed
replacement battery
Watch the video



05 Surface mounted
replacement lens
Watch the video



01



02



03



04



05




Serenga 2

Project covering & stylish



Escape route - Recessed (long beam)

- Up to 12 metres height
- 3 metres ceiling height: 23 metres spacing
- Harmonizing with interior spaces
- Long or wide beam + wall version



Luminaire data


Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)	Version
CTSR2-DEA-M3	REC M3 CT-NAVEO ESC-L4M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	0.6	○
CTSR2Q-DEA-M3	REC-SQ M3 CT-NAVEO ESC-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	□
SR2-DEA-230	REC 230V ESC-L4M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.4	○
SR2-DEA-230LT	REC 230V EMEX ESC-L4M WH	220-240 AC 50/60Hz			23	230V	0-40	0.4	○
SR2-DEA-M3	REC M3 AUTOTST ESC-4MH WH	220-240 AC 50Hz			21	3	5-40	0.6	○
SR2Q-DEA-230	REC-SQ 230V ESC L4M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.4	□
SR2Q-DEA-230LT	REC-SQ 230V EMEX ESC-L4M WH	220-240 AC 50/60Hz			23	230V	0-40	0.4	□
SR2Q-DEA-M3	REC-SQ M3 AUTOTST ESC-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	□
DASR2-DEA-M3	REC M3 DALI ESC-4MH WH	220-240 AC 50Hz			21	3	5-40	0.6	○

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including lens A. Black version available on request.




Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

IP Rating	Product type
IP20	flush mount from above
IP42	flush mount from below

Square cover



Round cover




Serenga 2

Project covering & stylish



Emergency spot light - Recessed (object lighting)

- Up to 12 metres height
- 3 metres ceiling height: 23 metres spacing
- Harmonizing with interior spaces
- Long or wide beam + wall version



Luminaire


Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)	Version
CTSR2-DSB-M3	REC M3 CT-NAVEO SPOT WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	0.6	○
CTSR2Q-DSB-M3	REC-SQ M3 CT-NAVEO SPOT WH	220-240 AC 50Hz			21	3	5-40	0.6	□
SR2-DSB-230	REC 230V ESC- SPOT WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.4	○
SR2-DSB-230LT	REC 230V EMEX ESC- SPOT WH	220-240 AC 50/60Hz			23	230V	0-40	0.4	○
SR2-DSB-M3	REC M3 AUTOTST ESC - SPOT WH	220-240 AC 50Hz			21	3	5-40	0.6	○
SR2Q-DSB-230	REC - SQ 230V ESC- SPOT WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.4	□
SR2Q-DSB-230LT	REC - SQ 230V EMEX ESC- SPOT WH	220-240 AC 50/60Hz			23	230V	0-40	0.4	□
SR2Q-DSB-M3	REC - SQM3 AUTOTST ESC - SPOT WH	220-240 AC 50Hz			21	3	5-40	0.6	□

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including Lens B. Black version available on request.




Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

IP Rating	Product type
IP20	flush mount from above
IP42	flush mount from below

Square cover



Round cover




Serenga 2

Project covering & stylish



Anti-panic lighting - Recessed (wide beam)

- Up to 12 metres height
- 3 metres ceiling height: 23 metres spacing
- Harmonizing with interior spaces
- Long or wide beam + wall version



Luminaire


Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)	Version
CTSR2-DAD-M3	REC M3 CT-NAVEO OA-L4M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	0.6	○
CTSR2Q-DAD-M3	REC-SQ M3 CT-NAVEO OA-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	□
SR2-DAD-230	REC 230V OA-L4M WH	220-240 AC/DC 0-60Hz			23	230V	5-40	0.4	○
SR2-DAD-230LT	REC 230V EMEX OA-L4M WH	220-240 AC 50/60Hz			23	230V	5-40	0.4	○
SR2-DAD-M3	REC M3 AUTOTST OA-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	○
SR2Q-DAD-230	REC-SQ 230V OA-L4M WH	220-240 AC/DC 0-60Hz			23	230V	5-40	0.4	□
SR2Q-DAD-230LT	REC-SQ 230V EMEX OA-L4M WH	220-240 AC 50/60Hz			23	230V	5-40	0.4	□
SR2Q-DAD-M3	REC-SQ M3 AUTOTST OA-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	□
DASR2-DAD-M3	REC M3 DALI OA-L4M WH	220-240 AC 50Hz			21	3	5-40	0.6	○

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including Lens D. Black version available on request.




Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

IP Rating	Product type
IP20	flush mount from above
IP42	flush mount from below

Square cover



Round cover




Serenga 2

Project covering & stylish





- Escape route - Surface mount (long beam)**
- Up to 12 metres height
 - 3 metres ceiling height: 23 metres spacing
 - Harmonizing with interior spaces
 - Long or wide beam + wall version



Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SEM3-A1	SFC M3 CT-NAVEO ESC-L4M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	1.0
SR2-SE230-A1	SFC 230V ESC-L4M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.7
SR2-SE230LT-A1	SFC 230V EMEX ESC-L4M WH	220-240 AC 50/60Hz			23	230V	0-40	0.7
SR2-SEM3-A1	SFC M3 AUTOTST ESC-L4M WH	220-240 AC 50Hz			21	3	5-40	1.0
DASR2-SEM3-A1	SFC M3 DALI ESC-L4M WH	220-240 AC 50Hz			21	3	5-40	1.0

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including lens A. Black version available on request.




Serenga 2

Project covering & stylish




- Anti-panic - Surface mount (wide beam)
- Up to 12 metres height
 - 3 metres ceiling height: 23 metres spacing
 - Harmonizing with interior spaces
 - Long or wide beam + wall version



Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SAM3-D1	SFC M3 CT-NAVEO OA-L4M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	1.0
SR2-SA230-D1	SFC 230V OA-L4M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.7
SR2-SA230LT-D1	SFC 230V EMEX OA-L4M WH	220-240 AC 50/60Hz			23	230V	0-40	0.7
SR2-SAM3-D1	SFC M3 AUTOTST OA-L4M- WH	220-240 AC 50Hz			21	3	5-40	1.0
DASR2-SAM3-D1	SFC M3 DALI OA-L4M WH	220-240 AC 50Hz			21	3	5-40	1.0

Designed and manufactured to meet the requirements of BS EN 60598.2.22
Including lens D. Black version available on request.



Serenga 2

Project covering & stylish





- Escape route - Surface mount 12m (long beam)**
- Up to 12 metres height
 - 3 metres ceiling height: 23 metres spacing
 - Harmonizing with interior spaces
 - Long or wide beam + wall version



Luminaire


Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (mA)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SEM3-BC1	SFC M3 CT-NAVEO ESC-MH12M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	1.0
SR2-SE230-BC1	SFC 230V ESC-MH12M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.7
SR2-SE230LT-BC1	SFC 230V EMEX ESC-MH12M WH	220-240 AC 50/60Hz			23	230V	0-40	0.7
SR2-SEM3-BC1	SFC M3 AUTOTST ESC-MH12M WH	220-240 AC 50Hz			21	3	5-40	1.0

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including lens B & C. Black version available on request.



Serenga 2


Project covering & stylish



Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption		Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
					(mA)	(W)			
CTSR2-SAM3-EF1	SFC M3 CT-NAVEO OA-MH12M WH	220-240 AC 50Hz	1 x LED	203	21		3	5-40	1.0
SR2-SA230-EF1	SFC 230V OA-MH12M WH	220-240 AC/DC 0-60Hz			23	230V		0-40	0.7
SR2-SA230LT-EF1	SFC 230V EMEX OA-MH12M WH	220-240 AC 50/60Hz			23	230V		0-40	0.7
SR2-SAM3-EF1	SFC M3 AUTOTST OA-MH12M WH	220-240 AC 50Hz			21		3	5-40	1.0

Designed and manufactured to meet the requirements of BS EN 60598.2.22.
Including lens E & F. Black version available on request.



Serenga 2

Project covering & stylish



Escape route - Surface mount wall


- Up to 12 metres height
- 3 metres ceiling height: 23 metres spacing
- Harmonizing with interior spaces
- Long or wide beam + wall version



Luminaire

			Lamp	Lamp	Power	Operation	Environment	Weight
Order code	Description	Input voltage	type	output (lm)	consumption (mA)	/ duration (hrs)	temp. (°C)	(kg)
CTSR2-SWM3-G1	SFC M3 CT-NAVEO WALL - W3M WH	220-240 AC 50Hz	1 x LED	203	21	3	5-40	1.0
SR2-SW230-G1	SFC230V WALL -W3M WH	220-240 AC/DC 0-60Hz			23	230V	0-40	0.7
SR2-SW230LT-G1	SFC 230V EMEX WALL - W3M WH	220-240 AC 50/60Hz			23	230V	0-40	0.7
SR2-SWM3-G1	SFC M3 AUTOTST WALL -W3M WH	220-240 AC 50Hz			21	3	5-40	1.0

Designed and manufactured to meet the requirements of BS EN 60598.2.22
Including lens G. Black version available on request.



Technical reference

Spacing data

Serenga SR2, emergency spot light

Point of emphasis - Disabled refuge see diagram 1

h (m)		Minimum lux
Self-contained		
2.5	1.6	7.2
2.8	1.8	7.2
3.2	1.9	6.3
3.7	2.1	5.5
4.0	2.3	5.05
Slave 230V		
2.5	1.5	8.2
2.8	1.7	7.1
3.2	2	6.6
3.7	2.3	5.9
4.0	2.4	5.7

Serenga SR2, emergency spot light

Point of emphasis - Call point see diagram 2

h (m)		Minimum lux
Self-contained		
2.5	1.5	15.5
2.8	1.7	12.7
3.2	1.9	8.15
3.7	2.1	5.56
4.0	-	-
Slave 230V		
2.5	1.5	17.8
2.8	1.75	13.3
3.2	2	9.5
3.7	2.4	6.64
4.0	2.4	5.7

Serenga SR2, emergency spot light

Point of emphasis - Telephone see diagram 3

h (m)		Minimum lux
Self-contained		
2.5	1	24.6
2.8	1.1	20.4
3.2	1.2	14.1
3.7	1.5	9.7
4.0	1.9	7.58
Slave 230V		
2.5	1	28.3
2.8	1.15	21.4
3.2	1.4	15.2
3.7	1.5	11.2
4.0	1.75	9.06

Serenga SR2, wall mount Lens G

Self contained and Slave (1,0lx) Slave (1,0lx)

h (m)				
Distance to escape route centre (t)				
		1m		1.5m
0.5	3.7	1.5	5.0	1.7
1.0	4.0	1.6	5.7	1.6
1.5	3.6	1.5	5.8	2.5
2.0	3.5	1.2	5.6	2.5
2.5	1.8	0.0	5.3	2.3
3.0	0.0	0.0	5.0	2.0
3.5	0.0	0.0	3.3	1.1






Diagram 1




D - Distance to wall (m)
H - Ceiling height (m)

Diagram 2



D - Distance to wall (m)
H - Ceiling height (m)

Diagram 3



D - Distance to (imaginary) vertical intercept (m)
H - Ceiling height (m)

Technical reference

Spacing data

Serenga 2, escape route lighting - lens A

h (m)				
Self Contained (1.0lx)				
2.0	1.8	4.9	6.4	18.8
2.5	1.3	5.3	6.4	19.4
3.0	1.0	5.0	3.9	18.3
3.5	0.9	3.9	3.6	16.6
4.0	0.9	3.1	2.5	15.6
Slave (1.0lx)				
2.0	2.0	5.2	7.0	19.7
2.5	1.6	5.6	6.9	20.8
3.0	1.2	5.5	4.8	20.0
3.5	1.1	4.8	4.0	19.7
4.0	1.0	3.7	3.2	16.8

Serenga 2, escape route lighting - lens B

h (m)				
Self Contained (1.0lx)				
4.5	1.6	4.2	6.9	17.4
5.0	1.6	4.4	7.1	18.3
5.5	1.6	4.5	7.3	19.1
6.0	1.6	4.6	7.1	19.8
6.5	1.5	4.7	7.2	20.3
7.0	1.4	4.7	7.0	20.5
7.5	1.3	4.7	7.0	20.7
8.0	1.1	4.6	6.7	20.7
Slave (1.0lx)				
4.5	1.7	4.4	7.4	17.8
5.0	1.7	4.6	7.7	19.0
5.5	1.8	4.7	7.8	19.9
6.0	1.7	4.9	7.6	20.7
6.5	1.6	5.0	7.7	21.3
7.0	1.6	5.0	7.7	21.8
7.5	1.5	5.0	7.5	22.0
8.0	1.4	5.0	7.4	22.1

Serenga 2, escape route lighting - lens C

h (m)				
Self Contained (1.0lx)				
8.5	2.0	5.8	7.1	17.0
9.0	1.9	5.8	7.3	17.7
9.5	1.7	5.9	7.4	18.3
10.0	1.2	5.9	7.5	18.9
10.5	0.0	6.0	0.0	14.1
11.0	0.0	5.2	0.0	12.6
11.5	0.0	4.5	0.0	12.2
12.0	0.0	4.0	0.0	12.0
Slave (1.0lx)				
8.5	2.1	6.1	7.6	17.4
9.0	2.1	6.2	7.8	18.1
9.5	2.0	6.2	7.9	18.8
10.0	1.9	6.2	8.1	19.4
10.5	1.5	6.3	7.9	20.0
11.0	0.4	6.4	8.0	20.6
11.5	0.0	6.4	0.0	14.0
12.0	0.0	5.2	0.0	13.3

Serenga 2, open area - lens D

h (m)				
Self Contained (0.5lx)				
2.0	3.9	8.1	3.9	8.1
2.5	4.6	10.0	4.6	10.0
3.0	5.4	11.6	5.4	11.6
3.5	6.0	13.2	6.0	13.2
4.0	6.6	14.8	6.6	14.8
Slave (0.5lx)				
2.0	3.9	8.2	3.9	8.2
2.5	4.6	10.0	4.6	10.0
3.0	5.4	11.8	5.4	11.8
3.5	6.3	13.4	6.3	13.4
4.0	6.9	15.0	6.9	15.0

Serenga 2, open area - lens E

h (m)				
Self Contained (0.5lx)				
4.5	5.0	11.0	5.0	11.0
5.0	5.3	12.0	5.3	12.0
5.5	5.5	12.9	5.5	12.9
6.0	5.8	13.7	5.8	13.7
6.5	5.6	14.4	5.6	14.4
7.0	4.2	14.3	4.2	14.3
7.5	3.6	14.1	3.6	14.1
8.0	3.2	14.1	3.2	14.1
Slave (0.5lx)				
4.5	5.0	11.2	5.0	11.2
5.0	5.3	12.2	5.3	12.2
5.5	5.7	13.1	5.7	13.1
6.0	6.0	14.0	6.0	14.0
6.5	6.0	14.7	6.0	14.7
7.0	8.8	15.5	8.8	15.5
7.5	4.5	15.3	4.5	15.3
8.0	4.1	15.2	4.1	15.2

Serenga 2, open area - lens F

h (m)				
Self Contained (0.5lx)				
8.5	4.7	11.4	4.7	11.4
9.0	4.8	11.7	4.8	11.7
9.5	4.8	12.0	4.8	12.0
10.0	5.1	12.4	5.1	12.4
10.5	5.1	12.7	5.1	12.7
11.0	5.1	12.9	5.1	12.9
11.5	5.1	13.2	5.1	13.2
12.0	5.3	13.5	5.3	13.5
Slave (0.5lx)				
8.5	4.9	11.8	4.9	11.8
9.0	5.0	12.1	5.0	12.1
9.5	5.0	12.5	5.0	12.5
10.0	5.3	12.8	5.3	12.8
10.5	5.3	13.1	5.3	13.1
11.0	5.4	13.5	5.4	13.5
11.5	5.6	13.7	5.6	13.7
12.0	5.6	14.0	5.6	14.0

Legend

	Tested and certified by an independent European certification agency such as KEMA		Indicates ingress protection class (IP value)
	BSI Kitemark approved		Self-contained: in case of power failure, the luminaire is battery powered
	Maintained / Switched maintained luminaire		Indicates the viewing distance of the (illuminated) pictogram in metres
	Non-maintained luminaire		3 hours autonomy (battery-powered light operating time)
	Insulation class II. This luminaire must not be earthed		Available with Naveo addressable, testing and remote management facility
	Self-Test product		NiMH Battery
	Product comes with an LED light source		Rear plate
	Surface mounted luminaire		Suspension kit
	Recess mounted luminaire		DALI compatible product





new.abb.com/middle-east
new.abb.com/africa