

TECHNICAL DATA SHEET

Stanilite®

Platinum exit LED Quickfit® weatherproof



Range

Platinum range

Product group

Exit LED Quickfit



Features



- 5 year warranty
- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- IP65 weatherproof enclosure
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Quickfit unique steel slide connect bracket for quick installation and easy maintenance
- UV stabilised vandal resistant polycarbonate cover or high impact chemical resistant acrylic cover option
- Can be wall or ceiling mounted and optional bracket kits available for strengthened wall and cantilever mounting
- Not suitable for installations where exposure to direct sunlight may occur

Catalogue no.	Description
Standard products	
PWQFLEDP-1P	Platinum exit LED Quickfit weatherproof single sided polycarbonate picto
PWQFLEDP-2P	Platinum exit LED Quickfit weatherproof single sided polycarbonate <picto
PWQFLEDP-3P	Platinum exit LED Quickfit weatherproof single sided polycarbonate picto>
PWQFLEDP-5P	Platinum exit LED Quickfit weatherproof double sided polycarbonate picto
PWQFLEDP-6P	Platinum exit LED Quickfit weatherproof double sided polycarbonate picto AOW
PWQFLEDA-1P	Platinum exit LED Quickfit weatherproof single sided acrylic picto
PWQFLEDA-2P	Platinum exit LED Quickfit weatherproof single sided acrylic <picto
PWQFLEDA-3P	Platinum exit LED Quickfit weatherproof single sided acrylic picto>
PWQFLEDA-5P	Platinum exit LED Quickfit weatherproof double sided acrylic picto
PWQFLEDA-6P	Platinum exit LED Quickfit weatherproof double sided acrylic picto AOW
Accessories	
WQFCLH	Cantilever mounting bracket - heavy duty
WQFCLL	Cantilever mounting bracket - light duty
WQFWM	Wall mount bracket
29-PIQFVERT	Quickfit pictograph vertical insert pack 4 piece set *
Note: * Refer to the installation manual for vertical installation requirements	
Spare parts	
03-01302P	Battery LiFePO4 3.2V 3.2Ah



Dimensions		
Length	Width	Height
466mm	155mm	274mm
Weight		
Model	Weight	
Standard	3.6kg	

Construction			
	Part	Construction	
	Body	Black UV/FR polycarbonate	
	Diffuser	Opal acrylic	
	Bracket	Black powder coated zinc steel	
	Enclosure cover	UV polycarbonate or high impact acrylic	
	Enclosure base	Black glass reinforced UV stabilised nylon	
Light source			
	Model	Light source	
	Standard	Multiple LED 1.6W	
Power consumption			
	Model	Power consumption	
	Standard	3.2W	
Photometrics			
	Model	Class	Classification
	Standard	C0	D3.2
		C90	D3.2

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards