TECHNICAL DATA SHEET

Stanilite®

Economy batten standard emergency

e-Range




Range
Economy range

Product group
Batten

Features
- 1 year warranty
- Electronic control gear
- HPF - high power factor
- High temperature NiCad batteries
- Optional acrylic prismatic diffuser or white galvanised steel wire guard

Catalogue no.	Description
Standard products	
ECBT118M	Economy batten 1x18W T8 maintained
ECBT118N	Economy batten 1x18W T8 non-maintained
ECBT218M	Economy batten 2x18W T8 maintained
ECBT218S	Economy batten 2x18W T8 sustained
ECBT136M	Economy batten 1x36W T8 maintained
ECBT136N	Economy batten 1x36W T8 non-maintained
ECBT236M	Economy batten 2x36W T8 maintained
ECBT236S	Economy batten 2x36W T8 sustained
	Note: Lamps not supplied
Accessories	
PR18	Diffuser kit to suit 18W battens
PR136	Diffuser kit to suit 1x36W battens
PR236	Diffuser kit to suit 2x36W battens
WG18	Wire guard kit to suit 18W battens
WG136	Wire guard kit to suit 1x36W battens
WG236	Wire guard kit to suit 2x36W battens
Spare parts	
03-01015P	Battery 3 cell NiCad 3.6V 4.0Ah (suits 18W)
03-01001P	Battery 4 cell NiCad 4.8V 4.0Ah (suits 36W)



Dimensions

Model	Length	Width	Bare height	Diffused height	Wire guard height
18W	615mm	123mm	82mm	132mm	132mm
1x36W	1225mm	65mm	82mm	132mm	132mm
2x36W	1225mm	120mm	82mm	132mm	132mm

Weight

Model	Weight
18W	3.0kg
1x36W	3.5kg
2x36W	4.0kg

Construction

Part	Construction
Body	White powder coated steel
Diffuser	Acrylic prismatic
Wire guard	Galvanised white powder coated

Photometrics

Model	Class	Bare	Diffused	Wire guard
ECBT118M	C0	D25	D20	D20
	C90	C25	C16	C20
ECBT118N	C0	D25	D20	D20
	C90	C25	C16	C20
ECBT218M	C0	D40	D32	D32
	C90	D16	C50	C40
	C180	D50	D50	D40
ECBT218S	C0	D20	D20	D20
	C90	C20	C12.5	C20
	C180	D16	D12.5	D12.5
ECBT136M	C0	D63	D32	D32
	C90	D20	C32	D12.5
ECBT136N	C0	D40	D32	D32
	C90	C40	C32	D12.5
ECBT236M	C0	D63	D50	D50
	C90	D25	D20	D20
	C180	D63	D63	D63
ECBT236S	C0	D40	D40	D32
	C90	C25	C32	C40
	C180	D32	D25	D25

Note: Preliminary results

Note:
- Designed to comply with AS2293 and meet relevant Australian EMC standards

ABB Australia Pty Limited
Phone: 1800 60 20 20
E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.
Copyright © 2018 ABB
All rights reserved

9AKK106713A9340 - Oct 2018