

Spitfire® LED

Signature Spitfire LED weatherproof non-maintained



Range


Signature range

Product group

Spitfire® LED

Features

- 3 year warranty
- Superior photometric classification
- LED technology 100,000 hours lamp life
- Single or dual LED option
- Polycarbonate IP67 weatherproof enclosure
- High temperature NiCad batteries
- Surface mount
- Low maintenance - ideal for carpark and coolrooms



Standard products

Catalogue no.	Description
SFBWP1LED	LED Spitfire single weatherproof surface mount
SFBWP2LED	LED Spitfire dual weatherproof surface mount

Spare parts

Catalogue no.	Description
03-01220	Battery 5 cell NiCad 6.0V 1.8Ah

Dimensions

Length	Width	Height
278mm	188mm	130mm

Weight

Model	Weight
Standard	2.8kg

Construction

Part	Construction
Lamp head	White polycarbonate
Weatherproof enclosure	Polycarbonate

Light source

Model	Light source
Single LED	2W
Dual LED	3W

Power consumption

Model	Power consumption
Standard	5.5W

Photometrics

Model	Class	Classification
Single LED	C0	D40
	C90	D40
Dual LED	C0	D50
	C90	D50

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

ABB Australia Pty Limited

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

Note: We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB
All rights reserved