

# Exit LED

## Signature exit LED Quickfit® vandal resistant



### Range


Signature range

### Product group

Exit LED

### Features

- 3 year warranty
- LED technology 100,000 hours lamp life
- IK09 mechanical impact resistance
- Vermin resistance
- Advanced pulsetime dual rate battery charger with high temperature NiCad batteries
- Unique internal steel slide connect bracket for quick installation and easy maintenance
- Strong steel body and end cap
- Anti-tamper cover screws
- Universal wall/ceiling mounting
- Includes all pictograph diffuser options for single or double sided installation



### Standard products

Catalogue no.	Description
VPQLED	LED Quickfit vandal resistant pictograph exit

### Spare parts

Catalogue no.	Description
03-01218	Battery 4 cell NiCad 4.8V 1.8Ah
PQFLED-FR	LED Quickfit exit frame only

### Dimensions

Length	Width	Height
410mm	140mm	265mm

### Weight

Model	Weight
Standard	7.8kg

### Construction

Part	Construction
Body and end cap	Steel body and end cap with anti-tamper cover screws White powder coated finish
Diffuser	Extra tough UV stabilised polycarbonate

### Light source

Model	Light source
Standard	Multiple LED 1.6W

### Power consumption

Model	Power consumption
Standard	3.6W

### Photometrics

Model	Class	Classification
Standard	C0	E1.25
	C90	E1.25

Note: Preliminary results

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

**ABB Australia Pty Limited**

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

**[www.stanilite.com.au](http://www.stanilite.com.au)**

**Note:** We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB  
All rights reserved