



Surgitron® I

1455-45 1455-80 1455-85

HEAVY DUTY SERVICE ENTRANCE APPLICATIONS MODULAR DESIGN

FEATURES AND BENEFITS

- Listed by ETL to UL 1449 3rd Edition for a Type 1 SPD application.
- Matrix of individually fused Metal Oxide Varistors (MOVs) housed in replaceable modules.
- Cover lights indicate status of modules.
- Model 1455-80 is recommended for sub-panels or for service entry when TNS neutral grounding is practiced.

Model Number	kA Per Phase	Voltage	Configuration		
1455-45	120kA	208/120V	3-Phase Wye, 4-Wire + Ground		
1455-80	120kA	208/120V	3-Phase Wye, 4-Wire + Ground		
1455-85	120kA	208/120V	3-Phase Wye, 4-Wire + Ground		
Warranty					
5-years					
Available Options					
Surge Counter		Add suffi	x -S		
Stainless Steel NEMA 4X enclosure Add suffix -4X					
Dry Relay Contacts come standard on 1455-80 and 1455-85 models only					
Stand Alone Option	n				
Remote Monitor		1260-97	,		

AVAILABLE CONFIGURATIONS

PRODUCT SPECIFICATIONS					
Electrical					
Nominal Discharge Current Rating (I-n)	20kA				
Operating Frequency	50-60Hz				
Connection Methods	Parallel to load (shunt)				
	Lugs #14-#2				
	Directly connect or through 60A (min) breaker				
Modes of Protection	1455-45 L-N, N-G				
	1455-80 L-N, L-G, N-G				
	1455-85 L-N, N-G				
Fault Rating (SCCR)	100kAIC				
Response Time	Less than 1 nanosecond (one per phase)				
Standard Monitoring	LED status indicator lights (one per phase)				
Mechanical					
Weight	28.7 lbs (13 kg)				
Enclosure Type	NEMA 4, 4X				
Installation Location	Indoor/Outdoor				
Mounting Method	Dual mounting flanges				
Operating Environment	-40° to +185°F (-40° to +85°C)				
Altitude	Up to 16,400 ft. (5000 m)				
Product Design	Individually fused MOVs				
	Overcurrent fusing				
Regulatory					
UL 1449 3rd Edition Type	Type 1				
UL 1283	No				
IEEE C62.41.1, .2, C62.45	Yes				
Listed By	ETL				




SURGITRON I PERFORMANCE DATA					
Model Number	kA Per Phase	Voltage Configuration	Protection Modes	MCOV	UL 1449 3rd Edition 6kV 3000A VPR
1455-45	120kA	208/120V	L-N	150	700V
			N-G	150	500V
1455-80	120kA	208/120V	L-N	150	700V
			L-G	150	700V
			N-G	150	500V
1455-85	120kA	208/120V	L-N	150	700V
			N-G	150	500V









DIMENSIONAL SPECIFICATIONS

Dim	Inches (mm)		
H1	14.75 (374.7)		
H2	15.5 (393.7)		
W1	12.9 (327.7)		
W2	10 (254)		
D	6.2 (157.5)		

